

LS-EMLSP (70,8X40) WH - Device marker




1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, white, unmarked, can be labeled with: TOPMARK LASER, TOPMARK NEO, mounting type: adhere, screw, rivet, Number of individual labels: 8, text field height: 40 mm, text field width: 70.8 mm



Your advantages

- Stick-on equipment marking with additional fixing holes
- Prefabricated device markers in the proven laser-sheet format for ideal positioning in the marking device

Commercial data

Item number	1069847
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG241D
Product key	BG241D
GTIN	4055626747743
Weight per piece (including packing)	39,62 g
Weight per piece (excluding packing)	38,28 g
Customs tariff number	39199080
Country of origin	DE

LS-EMLSP (70,8X40) WH - Device marker



1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Technical data

Product properties

Marking

Number of individual labels	8
Identification technology	Direct laser marking

Dimensions

Width	80.00 mm
Height	40.00 mm
Depth	0.80 mm

Text field

Text field width	70.8 mm
Text field height	40 mm

Material specifications

Foil strength	800 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Base element material	ABS
Components	free from silicone and halogen

Mechanical properties

Technical data

Drill hole spacing	74.00 mm
--------------------	----------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesa film test

LS-EMLSP (70,8X40) WH - Device marker



1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Weathering-resistance

Specification	DIN EN ISO 4892-2:2021-11
Result	Test passed
Test duration	6000 h
Procedure	A

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B

LS-EMLSP (70,8X40) WH - Device marker



1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Cycles	2
--------	---

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	adhere, screw, rivet
---------------	----------------------

LS-EMLSP (70,8X40) WH - Device marker



1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLSP (70,8X40) WH - Device marker



1069847

<https://www.phoenixcontact.com/nl/products/1069847>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl