

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe extension module for local bus extension, 1 function channel, TBUS interface, up to SIL 3, Cat. 4/PL e, plug-in Push-in terminal block, TBUS connector included

Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The extension module is for extending the local bus in the PSRmodular system. Therefore, additional extension modules can be integrated into the system that are at a certain distance from the base station.

Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Low housing width of just 22.6 mm
- Tool-free and time-saving installation thanks to Push-in technology

Commercial data

Item number	1105096
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA362
Product key	DNA362
GTIN	4055626975139
Weight per piece (including packing)	144 g
Weight per piece (excluding packing)	110 g
Customs tariff number	85371098
Country of origin	IT

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Application	Local bus extension
-------------	---------------------

Insulation characteristics

Protection class	III
------------------	-----

Insulation characteristics

Overvoltage category	II
----------------------	----

Degree of pollution	2
---------------------	---

Electrical properties

Maximum power dissipation for nominal condition	0.5 W
---	-------

Nominal operating mode	100% operating factor
------------------------	-----------------------

Interfaces	DIN rail TBUS for connection to the master module, supplied as standard
------------	---

Rated surge voltage/insulation	Basic insulation 4 kV between all current paths and housing
--------------------------------	---

Brake to be connected

Connection method	Push-in connection
-------------------	--------------------

Supply

Designation	A1/A2
-------------	-------

Rated control circuit supply voltage U_S	19.2 V DC ... 28.8 V DC
--	-------------------------

Rated control circuit supply voltage U_S	24 V DC -20 % / +20 % (provide external protection, typically 1 A)
--	--

Rated control supply current I_S	typ. 21 mA (at U_S)
------------------------------------	------------------------

Power consumption at U_S	typ. 0.5 W
----------------------------	------------

Inrush current	max. 8 A ($\Delta t = 200 \mu s$ at U_S)
----------------	--

Filter time	typ. 20 ms (in the event of voltage dips at U_S)
-------------	---

Protective circuit	Serial protection against polarity reversal
	Varistor

Connection data

Connection method	Push-in connection
-------------------	--------------------

Stripping length	10 mm
------------------	-------

Interfaces

Data: Local bus extension

Communication protocol	RS-485
------------------------	--------

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Connection method	Terminal block
Number of connections	1
Note	Note the requirements for the transmission cable in accordance with the data sheet section "Wiring".

Signaling

Status display	1 x LED (green)
Operating voltage display	1 x LED (green)
Error indication	2 x LED (red)

Dimensions

Width	22.61 mm
Height	107.74 mm
Depth	113.6 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-10 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	95 % (non-condensing)
Max. permissible relative humidity (operation)	95 % (non-condensing)
Shock	10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction)
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

CE

Identification	CE-compliant
----------------	--------------

Mounting

Mounting type	DIN rail mounting
Mounting position	vertical or horizontal

PSR-M-TBUS1-PI - Extension module


1105096

<https://www.phoenixcontact.com/nl/products/1105096>




Drawings

Application drawing



Block diagram



Block diagram

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1105096>



cULus Listed

Approval ID: E238705



Functional Safety

Approval ID: Z10029429 0013Rev.02

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Classifications

ECLASS

ECLASS-13.0	27371819
ECLASS-15.0	27371819

ETIM

ETIM 10.0	EC001449
-----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

PSR-M-TBUS1-PI - Extension module



1105096

<https://www.phoenixcontact.com/nl/products/1105096>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl