

Cable - FLK 50/2FLK20/EZ-DR/ 300/DV - 2304911

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled circular cable, with two 20-pos. and one 50-pos. socket strip (for Emerson Delta V). The cable is suitable for coupling 32-channel modules. Length of cable: 3 m

Why buy this product

- The DeltaV system can be used to install the process wiring via "mass termination blocks" (MTBs) using flat-ribbon cable plugs
- System cables specifically designed for 32-channel I/O modules with 40-pin MTB for connecting I/O modules to 32-channel VARIOFACE interface modules

Key Commercial Data

| | |
|--------------|---------------------|
| Packing unit | 1 STK |
| GTIN | 4 046356 011723 |

Technical data

General

| | |
|---|---|
| Nominal voltage U_N | < 50 V AC |
| | 60 V DC |
| Max. current carrying capacity per path | 1 A |
| Max. conductor resistance | 0.16 Ω/m |
| Length of cable | 3 m |
| Single wire, cross section | 0.14 mm ² |
| Single wire, cross section [AWG] | 26 |
| Conductor construction: Number of litz wires: | 7 |
| Single wire, material | Cu tin-plated |
| External diameter | 10.3 mm |
| Cable, preassembly | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding | no |

Environmental conditions

| | |
|---|-------------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-1 |
| | DIN VDE 0482 Part 332-1 |

Cable - FLK 50/2FLK20/EZ-DR/ 300/DV - 2304911

Technical data

Connector, module side

| | |
|-----------------------|--------------------------------|
| Connection method | IDC/FLK socket strip (2.54 mm) |
| Number of connections | 1 |
| Number of positions | 50 |

Connector, controller side

| | |
|-----------------------|--------------------------------|
| Connection method | IDC/FLK socket strip (2.54 mm) |
| Number of connections | 2 |
| Number of positions | 20 |

Supported controller

| | |
|---------------------|----------------|
| Controller | Emerson DeltaV |
| - suitable I/O card | VE4001S2T2B5 |
| | VE4002S1T2B6 |

Standards and Regulations

| | |
|------------------|-------------------------|
| Flame resistance | IEC 60332-1 |
| | DIN VDE 0482 Part 332-1 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27249205 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |

Cable - FLK 50/2FLK20/EZ-DR/ 300/DV - 2304911

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details

| |
|-----|
| EAC |
|-----|

| |
|-----|
| EAC |
|-----|

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>