

Starter kit - NLC-START-03 - 2701467

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



24 V DC base unit with relay outputs, LCD display, USB module, serial cable, input and output simulators and Quick Start Guide

Product Description

Kit containing items required to start programming and testing the Nanoline family of controllers.

Why buy this product

- Basic unit
- Operator panel
- Output simulator (available as 24 V AC or 24 V DC model)
- Input simulator (available as 24 V AC or 24 V DC model)
- USB cable

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 353588

Technical data

Product type	Starter kit
Set consists of	Base unit
	Operator terminal
	nanoLC module
	Cable
	Simulator card
	Simulator card

Starter kit - NLC-START-03 - 2701467

Articles in set

Base unit - NLC-055-024D-08I-04QRD-05A - 2700464



24 V DC Nanoline base unit. Equipped with 8 digital inputs, 2 analog (0-10 V) inputs and 4 relay output channels. Additional I/O channels can be added using a maximum of three I/O extension modules. Optional communication modules provide network or serial connectivity. Optional Operator Panel provides user interface. Programming is via nanoNavigator.

Operator terminal - NLC-OP1-LCD-032-4X20 - 2701137



User interface for Nanoline controllers. Mounts directly on the base unit. Can be mounted remotely using the mounting kit.

nanoLC module - NLC-MOD-USB - 2701195



Serial connection to PC's USB port for data transfer or software configuration

Cable - NLC-PC/USB-CBL 2M - 2701247



Cable, serial

Simulator card - NLC-050-24DC-IN-SIM - 2701357



Card to simulate inputs on an Nanoline base unit

Starter kit - NLC-START-03 - 2701467

Articles in set

Simulator card - NLC-050-24DC-OUT-SIM-R - 2701373

Card to simulate resistor outputs on a Nanoline base unit



Classifications

eCI@ss

eCI@ss 4.0	27250315
eCI@ss 4.1	27250315
eCI@ss 5.0	27242216
eCI@ss 5.1	27242216
eCI@ss 6.0	27242216
eCI@ss 7.0	27242216
eCI@ss 8.0	27242216

ETIM

ETIM 2.0	EC001417
ETIM 3.0	EC001417
ETIM 4.0	EC001417
ETIM 5.0	EC001417

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>