


# ZB 3,5,QR:FORTL.ZAHLEN 51-60 - Zack marker strip



0801405:0051

<https://www.phoenixcontact.com/nl/products/0801405:0051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, vertically labeled with the consecutive numbers: 51 ... 60, white, for terminal block width: 3.5 mm, mounting type: latching

The figure shows the ZB 3,5:UNBEDRUCKT, -LGS:FORTL.ZAHLEN, -QR:FORTL.ZAHLEN, and CUS versions

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0801405:0051  |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG2122        |
| Product key                          | BG2122        |
| GTIN                                 | 4046356665452 |
| Weight per piece (including packing) | 0,961 g       |
| Weight per piece (excluding packing) | 0,745 g       |
| Customs tariff number                | 49119900      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|       |        |
|-------|--------|
| Pitch | 3.5 mm |
|-------|--------|

### Marking

|           |           |
|-----------|-----------|
| Printing  | 51 ... 60 |
| Slot type | high      |

### Dimensions

|        |         |
|--------|---------|
| Width  | 3.5 mm  |
| Height | 10.5 mm |
| Depth  | 4.20 mm |
| Pitch  | 3.5 mm  |

### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 3.50 mm  |
| Text field height | 10.50 mm |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Base element material                  | PA                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesa film test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

# ZB 3,5,QR:FORTL.ZAHLEN 51-60 - Zack marker strip



0801405:0051

<https://www.phoenixcontact.com/nl/products/0801405:0051>

## Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 96 h                  |
| Temperature for testing | 120 °C                |

## Wipe resistance of inscriptions

|                                                 |                                                                                        |
|-------------------------------------------------|----------------------------------------------------------------------------------------|
| Specification                                   | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                     | Test passed                                                                            |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                                                            |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                                                            |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |                                               |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h                                          |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# ZB 3,5,QR:FORTL.ZAHLEN 51-60 - Zack marker strip



0801405:0051

<https://www.phoenixcontact.com/nl/products/0801405:0051>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# ZB 3,5,QR:FORTL.ZAHLEN 51-60 - Zack marker strip



0801405:0051

<https://www.phoenixcontact.com/nl/products/0801405:0051>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.

Hengelder 56 6902 PA Zevenaar

Postbus 246 6900 AE Zevenaar

(0316) 59 17 20

[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)