

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Roll, white, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, unperforated, mounting type: latching, snap into flat marker groove, for terminal block width: 100 mm, Number of individual labels: 1000, text field height: 6.35 mm, text field width: 101.5 mm

## Your advantages

- The TMT labeling range includes markers for all products with tall and flat marker grooves
- The perforated marking strips are easy to separate and can be easily fitted using the tool supplied
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all TMT ... markers in accordance with your requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0816605       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG2111        |
| Product key                          | BG2111        |
| GTIN                                 | 4046356107389 |
| Weight per piece (including packing) | 456 g         |
| Weight per piece (excluding packing) | 456 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

## Technical data

### Product properties

|       |        |
|-------|--------|
| Pitch | 100 mm |
|-------|--------|

### Marking

|                                     |                  |
|-------------------------------------|------------------|
| Number of individual labels         | 1000             |
| Number of individual labels per row | 1                |
| Slot type                           | flat             |
| Identification technology           | Thermal transfer |

### Dimensions

|        |           |
|--------|-----------|
| Width  | 100.00 mm |
| Height | 6.35 mm   |
| Depth  | 0.17 mm   |
| Pitch  | 100 mm    |

### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 101.5 mm |
| Text field height | 6.35 mm  |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Foil strength         | 175 µm                         |
| Color                 | white (RAL 9010)               |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                         |
|-------------------------------------------------------------------|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result                                                            | Test passed             |

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 96 h                  |
| Temperature for testing | 120 °C                |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 150 °C (180 °C) | Test passed                     |

## Wipe resistance of inscriptions

|                                                   |                                                                                        |
|---------------------------------------------------|----------------------------------------------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed                                                                            |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                                                            |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                                                            |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                                                            |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                                                            |

## Immersion in chemicals, oil & fuel

|                                                   |                          |
|---------------------------------------------------|--------------------------|
| Specification                                     | ISO 175:2010 (following) |
| Test duration                                     | 168 h                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed              |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ]     | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed              |
| Gasoline<br>[CAS No. 64742-49-0]                  | Test passed              |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed              |
| IRM 901                                           | Test passed              |
| IRM 902                                           | Test passed              |
| IRM 903                                           | Test passed              |

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |                                               |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h                                          |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# TMT 100 R - Marker for terminal blocks



0816605

<https://www.phoenixcontact.com/nl/products/0816605>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.

Hengelder 56 6902 PA Zevenaar

Postbus 246 6900 AE Zevenaar

(0316) 59 17 20

[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)