

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched TRIO power supply for DIN rail mounting, input: 3-phase, output: 72 V DC/14 A, dynamic boost, tool-free fast connection technology for rigid and flexible conductors with ferrule

## Product description

TRIO POWER power supplies with standard functionality

The TRIO POWER power supply range with push-in connection has been perfected for use in machine building. All functions and the space-saving design of the single and three-phase modules are optimally tailored to the stringent requirements. Under challenging ambient conditions, the power supply units, which feature an extremely robust electrical and mechanical design, ensure the reliable supply of all loads.

## Your advantages

- Very cost-effective with time-saving, tool-free Push-in connection and a slim design
- Reliable startup of difficult loads with the dynamic power reserve, providing 150% of the nominal current for a maximum of 5 s
- Electrically robust, thanks to high electric strength
- Mechanically robust, thanks to high vibration and shock resistance

## Commercial data

Item number	1076188
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMPO39
GTIN	4055626783918
Weight per piece (including packing)	3,070 g
Weight per piece (excluding packing)	2,600 g
Customs tariff number	85044095
Country of origin	CN

## Technical data

### Input data

#### AC operation

Network type	Star network
Nominal input voltage range	3x 400 V AC ... 500 V AC
Input voltage range	3x 400 V AC ... 500 V AC -20 % ... +15 %
Typical national grid voltage	3x 400 V AC 3x 480 V AC
Voltage type of supply voltage	AC
Inrush current	≤ 30 A (typical)
Inrush current integral ( $I^2t$ )	< 1.1 A <sup>2</sup> s
Inrush current limitation	35 A (after 1 ms)
AC frequency range	50 Hz ... 60 Hz
Frequency range ( $f_N$ )	50 Hz ... 60 Hz ±5 Hz
Mains buffering time	> 10 ms (400 V AC) > 20 ms (480 V AC)
Current consumption	3x 1.9 A (400 V AC) 3x 1.7 A (500 V AC)
Nominal power consumption	1335.1 VA
Protective circuit	Transient surge protection; Varistor
Power factor (cos phi)	0.77
Typical response time	< 1 s
Input fuse	6.3 A (internal (device protection))
Recommended breaker for input protection	10 A ... 16 A (Characteristics B, C, D, K)
Discharge current to PE	< 3.5 mA < 2.5 mA (550 V AC, 60 Hz)

### Output data

Efficiency	> 94.6 % (400 V AC) > 94.3 % (480 V AC)
Output characteristic	U/I with dynamic load reserve
Nominal output voltage	72 V DC ±1 %
Setting range of the output voltage ( $U_{Set}$ )	70 V DC ... 85 V DC (> 72 V DC, constant capacity restricted)
Nominal output current ( $I_N$ )	14 A
Dynamic Boost ( $I_{Dyn.Boost}$ )	21 A (5 s)
Derating	> 60 °C ... 70 °C (2.5 %/K)
Feedback voltage resistance	< 105 V DC
Protection against overvoltage at the output (OVP)	≤ 105 V DC
Control deviation	< 1 % (change in load, static 10 % ... 90 %) < 3 % (Dynamic load change 10 % ... 90 %, 10 Hz) < 0.1 % (change in input voltage ±10 %)
Residual ripple	≤ 300 mV <sub>PP</sub>

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Short-circuit-proof	yes
No-load proof	yes
Output power	1008 W
	1512 W (5 s)
Maximum no-load power dissipation	< 7 W (400 V AC)
Power loss nominal load max.	< 58 W (400 V AC)
Short-circuit current	< 23.5 A DC (permanent)
Rise time	≤ 2 ms (U <sub>OUT</sub> (10 % ... 90 %))
Connection in parallel	yes
Connection in series	yes

Signal: DC OK

Continuous load current	100 mA
-------------------------	--------

Signal relay 13/14

Default	closed
Digital	30 V AC 30 V DC 100 mA

## Connection data

Input

Connection method	Push-in connection
Conductor cross section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross section, rigid max.	4 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	4 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, max.	2.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	10 mm

Output

Connection method	Push-in connection
Conductor cross section, rigid min.	0.75 mm <sup>2</sup>
Conductor cross section, rigid max.	16 mm <sup>2</sup>
Conductor cross section flexible min.	0.75 mm <sup>2</sup>
Conductor cross section flexible max.	16 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, min.	0.75 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, max.	10 mm <sup>2</sup>

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Single conductor/flexible terminal point with ferrule without plastic sleeve, min.	0.75 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, max.	16 mm <sup>2</sup>
Conductor cross section AWG min.	20
Conductor cross section AWG max.	4
Stripping length	18 mm

## Signal

Connection method	Push-in connection
Conductor cross section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross section, rigid max.	0.75 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	1.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, max.	0.75 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, max.	1 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	18
Stripping length	8 mm

## Signaling

Types of signaling	LED
	Floating signal contact

## Signal output: LED status indicator

Signalization designation	DC OK
Status display	LED
Color	green
DC OK	$U_{OUT} > 0.95 \times U_N$ ( $U_N = 72$ V DC)

## Electrical properties

Number of phases	3
Insulation voltage input/output	3 kV AC (type test)
	1.5 kV AC (routine test)

## Product properties

Product type	Power supply
Product family	TRIO POWER
MTBF (IEC 61709, SN 29500)	> 1730000 h (25 °C)
	> 1051000 h (40 °C)
	> 510000 h (60 °C)

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

## Insulation characteristics

Protection class	I (in closed control cabinet)
Degree of pollution	2

## Dimensions

Width	110 mm
Height	130 mm
Depth	160 mm

## Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	50 mm / 50 mm

## Mounting

Mounting type	DIN rail mounting
Assembly note	alignable: horizontally 0 mm ( $\leq 40\text{ }^{\circ}\text{C}$ ) 10 mm ( $\leq 70\text{ }^{\circ}\text{C}$ ), vertically 50 mm
Mounting position	horizontal DIN rail NS 35, EN 60715
With protective coating	no

## Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Plastic
Type of housing	Aluminum (AlMg3)
Hood version	Polycarbonate

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (> 60 °C Derating: 2,5 %/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (start-up type tested)	-40 °C
Maximum altitude	$\leq 4000\text{ m}$ (> 2000 m, Derating: 10 %/1000 m)
Climatic class	3K3 (in acc. with EN 60721)
Max. permissible relative humidity (operation)	$\leq 95\text{ }%$ (at 25 °C, non-condensing)
Shock	11 ms, 15 g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude $\pm 2.5\text{ mm}$ (according to IEC 60068-2-6) 15 Hz ... 150 Hz, 0.7g, 90 min.

## Standards and regulations

Standard – Limitation of mains harmonic currents	EN 61000-3-2
Standard - Electrical safety	IEC 61010-2-201
Standard - Safe isolation	DIN VDE 0100-410

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Standard - Safety of transformers	EN 61558-2-16 (air clearances and creepage distances only)
Overvoltage category	
EN 61010-1	II ( $\leq 2000$ m)

## Approvals

UL approvals	UL/C-UL Listed UL 61010-1
Conformity/Approvals	
SIL in accordance with IEC 61508	0

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Interference emission	Interference emission in accordance with EN 61000-6-3 (residential and commercial) and EN 61000-6-4 (industrial)
EMC requirements for noise immunity	EN 61000-6-1
	EN 61000-6-2

### Conducted noise emission

Standards/regulations	EN 55016-2-1
	EN 61000-6-4 (Class A)

### Noise emission

Standards/regulations	EN 55011 (EN 55022)
-----------------------	---------------------

### Noise emission

Standards/regulations	EN 55016-2-3
	EN 61000-6-4 (Class A)

### Harmonic currents

Standards/regulations	EN 55016-2-3
	EN 61000-3-2 (Class A)

### Flicker

Standards/regulations	EN 61000-3-3
	EN 61000-3-3

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Contact discharge	6 kV (Test Level 3)
Discharge in air	8 kV (Test Level 3)
Comments	Criterion A

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

### Electromagnetic HF field

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 2 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	2 GHz ... 6 GHz
Test field strength	10 V/m (Test Level 3)
Comments	Criterion A

## Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

## Fast transients (burst)

Input	4 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Signal	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion A

## Surge voltage load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Surge voltage load (surge)

Input	2 kV (Test Level 4 - symmetrical)
	4 kV (Test Level 4 - asymmetrical)
Output	1 kV (Test Level 3 - symmetrical)
	2 kV (Test Level 3 - asymmetrical)
Signal	1 kV (Test Level 2 - asymmetrical)
Comments	Criterion A

## Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

## Conducted interference

Input/Output	asymmetrical
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)

## Voltage dips

Standards/regulations	EN 61000-4-11
Voltage	400 V AC
Frequency	50 Hz
Voltage dip	70 %
Number of periods	25 periods
Comments	Criterion A
Voltage dip	40 %
Number of periods	10 periods
Comments	Criterion A

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

Voltage dip	0 %
Number of periods	1 period
Comments	Criterion A

## Emitted interference


Standards/regulations	EN 61000-6-3
Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential

## Criteria


Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.
Criterion C	Temporary adverse effects on the operating behavior, which the device corrects automatically or which can be restored by actuating the operating elements.

Drawings

Diagram



Block diagram



# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1076188>



**UL Listed**

Approval ID: E123528



**cUL Listed**

Approval ID: E123528



**EAC**

Approval ID: RU S-DE.BL08.W.00764

# TRIO-PS-2G/3AC/72DC/14 - Power supply



1076188

<https://www.phoenixcontact.com/pc/products/1076188>

## Classifications

### ECLASS

ECLASS-13.0	27040701
ECLASS-15.0	27040701

### ETIM

ETIM 9.0	EC002540
----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

1076188

<https://www.phoenixcontact.com/pc/products/1076188>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
	Lead(CAS: 7439-92-1)
	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
SCIP	Lead(CAS: 7439-92-1) a5daa092-5f12-48d9-b905-347a11033d0d

### EF3.0 Climate Change

CO2e kg	63.85 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
 Flachsmarktstraße 8  
 D-32825 Blomberg  
 +49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)