

CK1,6-ED-1,00F AG - Crimp contact



1266296

<https://www.phoenixcontact.com/nl/products/1266296>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Socket, turned, contact diameter: 1.6 mm, connection cross section: 0.75 mm² ... 1 mm², AWG 18...18 , contact material: Cu alloy

Commercial data

Item number	1266296
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AF7AIA
Product key	AF7AIA
GTIN	4063151381158
Weight per piece (including packing)	0,734 g
Weight per piece (excluding packing)	0,734 g
Customs tariff number	85366990
Country of origin	CN

CK1,6-ED-1,00F AG - Crimp contact

1266296

<https://www.phoenixcontact.com/nl/products/1266296>



Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	For voltages less than 5 V and currents less than 5 mA, gold-plated contacts are recommended.

Product properties

Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
Contact material type	turned

Connection data

Connection technology

Contact connection type	Socket
Connection method	Crimp connection


Conductor connection

Stripping length	8 mm
Connection cross section (flexible)	0.75 mm ² ... 1 mm ²
Connection cross section	1 mm ² ... 1 mm ²
Connection cross section AWG	18 ... 18

Material specifications

Material Contact	Cu alloy (lead-free)
Material Contact surface	Ag

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

CK1,6-ED-1,00F AG - Crimp contact

1266296

<https://www.phoenixcontact.com/nl/products/1266296>



Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ED-1,00F AG - Crimp contact


1266296

<https://www.phoenixcontact.com/nl/products/1266296>



Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-1,00F AG - Crimp contact

1266296

<https://www.phoenixcontact.com/nl/products/1266296>



Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-1,00F AG - Crimp contact



1266296

<https://www.phoenixcontact.com/nl/products/1266296>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl