

MM-WML 3 (EX10)R C1 YE/BK - Cable marker label



1116137

<https://www.phoenixcontact.com/nl/products/1116137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker label, Roll, yellow/black, unmarked, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, cable diameter range: 2 ... 3 mm, mounting type: adhesive, cable diameter: ≤ 3 mm, Number of individual labels: 1, text field height: 8 mm, text field width: 6500 mm

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- Thanks to the continuous format, a wrap-around label of the appropriate width can be created flexibly for the relevant application
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The transparent protective foil is wound over the marking and provides permanent protection against contamination and abrasion
- The wrap-around labels do not add bulk, which means that the cable can still be drawn through cable ducts, for example
- The material is cUL certified

Commercial data

Item number	1116137
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG221E
Product key	BG221E
GTIN	4063151040758
Weight per piece (including packing)	80 g
Weight per piece (excluding packing)	68 g
Customs tariff number	96121020
Country of origin	CN

MM-WML 3 (EX10)R C1 YE/BK - Cable marker label



1116137

<https://www.phoenixcontact.com/nl/products/1116137>

Technical data

Product properties

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermal transfer

Dimensions

Height	18 mm
Length	6.5 m

Text field

Text field width	6500 mm
Text field height	8 mm

Material specifications

Foil strength	89 µm
Adhesive strength	23 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	yellow (RAL 1018)
	black (RAL 9005)
Material	Vinyl polymer
Base element material	Vinyl polymer
Components	Free from silicone and cadmium

Cable/line

External cable diameter	≤ 3.00 mm
	2 mm ... 3 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

MM-WML 3 (EX10)R C1 YE/BK - Cable marker label



1116137

<https://www.phoenixcontact.com/nl/products/1116137>

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

MM-WML 3 (EX10)R C1 YE/BK - Cable marker label



1116137

<https://www.phoenixcontact.com/nl/products/1116137>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1116137>



cULus Recognized

Approval ID: MH48542

MM-WML 3 (EX10)R C1 YE/BK - Cable marker label



1116137

<https://www.phoenixcontact.com/nl/products/1116137>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	4,055 kg CO2e
---------	---------------