

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PP-EPDM, gray RAL 7035, Plug straight M12, coding: A, on free cable end, cable length: 1.5 m, Hygienic design, with high-grade steel knurl

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Stainless steel type 1.4404 used to provide corrosion protection for all exposed metal parts
- Contamination can be detected quickly – thanks to the light color

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1403947       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF1CCA        |
| Product key                          | AF1CCA        |
| GTIN                                 | 4046356676946 |
| Weight per piece (including packing) | 59,8 g        |
| Weight per piece (excluding packing) | 50 g          |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

## Technical data

### Product properties

|                      |                          |
|----------------------|--------------------------|
| Application          | Food processing industry |
| Number of positions  | 4                        |
| No. of cable outlets | 1                        |
| Shielded             | no                       |
| Coding               | A                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                               |                 |
|-------------------------------|-----------------|
| Material of grip body         | PP              |
| Contact material              | CuSn            |
| Contact surface material      | Ni/Au           |
| Contact carrier material      | PP              |
| Material for screw connection | Stainless steel |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V AC                   |
|                       | 250 V DC                   |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |
| Coding type         | A                 |

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable




1403947

<https://www.phoenixcontact.com/nl/products/1403947>

## Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|                                               |                                                                                                                                        |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Cable length                                  | 1.5 m                                                                                                                                  |
| Dimensional drawing                           |                                                      |
| Cable weight                                  | 30 kg/km                                                                                                                               |
| Number of positions                           | 4                                                                                                                                      |
| Shielded                                      | no                                                                                                                                     |
| Conductor structure signal line               | 42x 0.10 mm                                                                                                                            |
| AWG signal line                               | 22                                                                                                                                     |
| Conductor cross-section                       | 4x 0.34 mm <sup>2</sup> (Signal line)                                                                                                  |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm (Signal line)                                                                                                         |
| External cable diameter                       | 4.70 mm ±0.15 mm                                                                                                                       |
| Outer sheath, material                        | PP-EPDM                                                                                                                                |
| External sheath, color                        | gray RAL 7035                                                                                                                          |
| Conductor material                            | Bare Cu litz wires                                                                                                                     |
| Material wire insulation                      | PP                                                                                                                                     |
| Single wire, color                            | brown, white, blue, black                                                                                                              |
| Thickness, insulation                         | ≥ 0.21 mm                                                                                                                              |
| Thickness, outer sheath                       | approx. 0.80 mm                                                                                                                        |
| Overall twist                                 | 4 wires, twisted                                                                                                                       |
| Length of twist, overall twist                | 48 mm                                                                                                                                  |
| Max. conductor resistance                     | approx. 58 Ω/km                                                                                                                        |
| Insulation resistance                         | ≥ 1 GΩ*km                                                                                                                              |
| Nominal voltage, cable                        | ≤ 300 V                                                                                                                                |
| Test voltage                                  | ≥ 3000 V                                                                                                                               |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                                  |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                                 |
| Smallest bending radius, fixed installation   | 24 mm                                                                                                                                  |
| Smallest bending radius, movable installation | 47 mm                                                                                                                                  |
| Dynamic load capacity (bending)               | Max. bending cycles: 4000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Dynamic load capacity (torsion)               | Torsion: ±270 °/m, Torsion cycles: ≥4000000, Torsional frequency: ≤25 Torsion cycles/min                                               |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815                                                                                               |

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

|                                 |                                                                                     |
|---------------------------------|-------------------------------------------------------------------------------------|
| Other resistance                | Resistant to cold bending and cold impacts (according to DIN EN 60811-1-4 (-40 °C)) |
| Special properties              | partly suitable for use with drag chain                                             |
| Ambient temperature (operation) | -40 °C ... 105 °C (cable, fixed installation)                                       |
|                                 | -25 °C ... 105 °C (Cable, flexible installation)                                    |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                   |
|-------------------------------------------------------------------|-----------------------------------|
| Degree of protection                                              | IP65                              |
|                                                                   | IP67                              |
|                                                                   | IP68                              |
|                                                                   | IP69K                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 105 °C (Plug / socket) |

## Standards and regulations

### M12

|                          |                      |
|--------------------------|----------------------|
| Standard designation     | M12 connector        |
| Standards/specifications | IEC 61076-2-101      |
| Standard designation     | Material conformance |
| Standards/specifications | FDA 21 CFR 177.2600  |

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable




1403947

<https://www.phoenixcontact.com/nl/products/1403947>


## Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

## Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1403947>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-4P-M12MS/1,5-600 HD - Sensor/actuator cable



1403947

<https://www.phoenixcontact.com/nl/products/1403947>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 0,52 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)