CUC-V06-C1PBK-S/R4CEA:1 - RJ45 connector

1414410

https://www.phoenixcontact.com/nl/products/1414410

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP67, number of positions: 8, 10 Gbps, $CAT6_A$, material: Plastic, connection method: Crimp connection, connection cross section: AWG 24- 27, cable outlet: straight, color: black, Ethernet/PROFINET

Commercial data

Item number	1414410
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABNNAB
Product key	ABNNAB
GTIN	4055626028323
Weight per piece (including packing)	18,4 g
Weight per piece (excluding packing)	16,324 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Type	RJ45
Sensor type	Ethernet/PROFINET
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	no
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1 A
Frequency range	to 500 MHz
Nominal voltage U_N	72 V (DC)
Nominal current I_N	1.75 A
Transmission medium	Copper
Transmission speed	10 Gbps (500 MHz)
Transmission characteristics (category)	$CAT6_A$
Transmission speed	10 Gbps

Connection data

Connection technology

Connection method	Crimp connection
Connection cross section AWG	24 ... 27 (flexible)
Conductor cross-section	0.1 mm² ... 0.2 mm² (flexible)

Dimensions

Width	38.4 mm
Height	53 mm
Length	19.9 mm

Material specifications

Color	black
Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material	TPE
Housing material	Plastic
Cable seal material	NBR

Contact material	Phosphor bronze
Contact surface material	Gold
Contact carrier material	PC
O-ring material	FPM

Cable/line

External cable diameter	5 mm ... 8.5 mm
Cable cross section	0.1 mm²


Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000

Drawings

Dimensional drawing



RJ45 sleeve housing IP67

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC004746

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	906cf7f2-b8b3-40bf-b5e6-8a4161715b63

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl