

# FOC-FDX20-PP-SCD6-OM3-PT9 - Splice box



1343381

<https://www.phoenixcontact.com/nl/products/1343381>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Splice box, design: Rail-mountable module, degree of protection: IP20, material: Metal, connection method: Splicing, cable outlet: above and below, housing size: 1, color: gray

DIN rail splice box 6x SC duplex, including pigtails and splice holder

## Product description

FDX 20 series DIN rail splice box, assembled with 6x SC duplex coupling, fully assembled and ready for splicing with pre-assembled 900 µm pigtails (OM3). Splice holder for separately available shrink and crimp splicing protection, on a patented splice comb made from powder-coated sheet steel. Cable insertion possible via cable gland from above or below. Housing, 2-part, prepared for DIN rail mounting through the rear-side adapter. The adapter can also be mounted on the side.

Scope of supply:

DIN rail housing with integrated splice comb (mounted), assembled with 6x SC duplex coupling, 12x pigtail (OM3), 1x splice holder, 1x cable gland (M20x1.5)

## Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- Flexible DIN rail mounting possible in six positioning directions
- Suitable for industrial applications
- Continuously reliable data connection, thanks to extensively tested components
- Snap-on mounting on standard DIN rails NS 35/7.5 or NS 35/15
- Perfectly sized and patented pigtail tray for convenient splicing and compact bending radii.
- Particularly suitable for fusion splicing
- For easy field connection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1343381       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | ABNGAA        |
| Product key                          | ABNGAA        |
| GTIN                                 | 4063151654948 |
| Weight per piece (including packing) | 713,2 g       |
| Weight per piece (excluding packing) | 646,651 g     |
| Customs tariff number                | 85367000      |
| Country of origin                    | DE            |

## Technical data

### Notes

|                    |                                                                                                                                      |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Order information: | In addition, shrink splice protection (Item No.: 1019676) or crimp splice protection (Item No.: 1019678) must be ordered separately. |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------|

### Product properties

|                              |                       |
|------------------------------|-----------------------|
| Series                       | FDX 20 series         |
| Type                         | Rail-mountable module |
| Connection profile           | SC-Duplex             |
| No. of cable outlets         | 2                     |
| No. of conductors            | 12                    |
| Number of module slots       | 6                     |
| Number of slots              | 12                    |
| Type of the screw connection | M20 x 1.5             |
| Protective cover             | yes                   |
| Cable outlet                 | above and below       |

### Electrical properties

|                     |          |
|---------------------|----------|
| Attenuation         | ≤ 0.3 dB |
| Transmission medium | FO       |

### Connection data

#### Connection technology

|                   |          |
|-------------------|----------|
| Connection method | Splicing |
|-------------------|----------|

### Dimensions

|        |        |
|--------|--------|
| Width  | 40 mm  |
| Height | 130 mm |
| Depth  | 115 mm |

#### Housing

|               |       |
|---------------|-------|
| Housing width | 40 mm |
|---------------|-------|

#### Mechanical characteristics

|                  |         |
|------------------|---------|
| Ferrule diameter | 2.50 mm |
|------------------|---------|

### Material specifications

|                                        |                     |
|----------------------------------------|---------------------|
| Color                                  | gray                |
| Flammability rating according to UL 94 | V0                  |
| Ferrule material                       | Zirconia ceramics   |
| Housing material                       | Metal               |
| Housing surface material               | Powder-coated, gray |

## Cable/line

|                                |                                                       |
|--------------------------------|-------------------------------------------------------|
| Cable type                     | Multimode fiberglass                                  |
| Cable type                     | 900 µm                                                |
| Cable structure                | semi-loose compact wires (STB)                        |
| External cable diameter        | 6 mm ... 12 mm                                        |
| External cable diameter        | 6 mm ... 12 mm                                        |
| Wire diameter incl. insulation | 900 µm                                                |
| Individual wire diameter       | 900 µm (250/900 µm)                                   |
| Single wire, color             | Assignment color-coded in accordance with IEC 60794-2 |
| Whip length                    | ≥ 1.5 m                                               |
| Halogen-free                   | yes                                                   |
| Resistance to oil              | no                                                    |
| Flame resistance               | yes                                                   |

## FO cable

|                     |                                |
|---------------------|--------------------------------|
| Number of fibers    | 12                             |
| Fiber               | GOF                            |
| Fiber type          | Multimode fiberglass 50/125 µm |
| Attenuation         | ≤ 0.3 dB                       |
| Return Loss         | ≥ 35 dB                        |
| Transmission medium | FO                             |

## Mechanical properties

## Mechanical data

|                              |           |
|------------------------------|-----------|
| Type of the screw connection | M20 x 1.5 |
| Insertion/withdrawal cycles  | ≥ 500     |
| Smallest bending radius      | 30 mm     |

## Characteristics

|             |          |
|-------------|----------|
| Attenuation | ≤ 0.3 dB |
|-------------|----------|

## Environmental and real-life conditions

## Ambient conditions

|                                         |                                   |
|-----------------------------------------|-----------------------------------|
| Degree of protection                    | IP20 (according to IEC 60529)     |
|                                         | IP20                              |
| Ambient temperature (operation)         | -40 °C ... 85 °C (Category OPhd+) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                  |
| Ambient temperature (assembly)          | 0 °C ... 55 °C                    |
| Resistance to oil                       | no                                |

## Standards and regulations

|                   |     |
|-------------------|-----|
| Flame resistance  | yes |
| Resistance to oil | no  |

# FOC-FDX20-PP-SCD6-OM3-PT9 - Splice box



1343381

<https://www.phoenixcontact.com/nl/products/1343381>

## Mounting

|               |                                                    |
|---------------|----------------------------------------------------|
| Mounting type | DIN rail mounting                                  |
| Assembly note | Option for flexible replugging of DIN rail adapter |

# FOC-FDX20-PP-SCD6-OM3-PT9 - Splice box



1343381

<https://www.phoenixcontact.com/nl/products/1343381>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1343381>



**UL Listed**

Approval ID: E335024-20250729



**cUL Listed**

Approval ID: E335024-20250729

# FOC-FDX20-PP-SCD6-OM3-PT9 - Splice box



1343381

<https://www.phoenixcontact.com/nl/products/1343381>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19170113 |
| ECLASS-15.0 | 19170113 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002699 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43223300 |
|-------------|----------|

# FOC-FDX20-PP-SCD6-OM3-PT9 - Splice box



1343381

<https://www.phoenixcontact.com/nl/products/1343381>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)