

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 5-position, PVC, gray RAL 7001, shielded (Advanced Shielding Technology), free cable end, on Socket angled M12, coding: L, cable length: 3 m, for direct current up to 16 A/63 V

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against mismatching, thanks to special L-coding
- Shield power reliably – 360° shielding to reduce electromagnetic loads

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1414795       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF1CDP        |
| Product key                          | AF1CDP        |
| GTIN                                 | 4055626034294 |
| Weight per piece (including packing) | 779,53 g      |
| Weight per piece (excluding packing) | 779,53 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

## Technical data

### Product properties

|                      |               |
|----------------------|---------------|
| Application          | Energy supply |
| Number of positions  | 5             |
| No. of cable outlets | 1             |
| Shielded             | yes           |
| Coding               | L             |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Material of grip body                  | PP                           |
| Contact material                       | CuZn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA                           |
| Material for screw connection          | Zinc die-cast, nickel-plated |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 63 V DC                    |
| Nominal current $I_N$ | 16 A                       |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

#### Connection 2

|             |                   |
|-------------|-------------------|
| Type        | Socket angled M12 |
| Coding type | L (Power)         |

### Cable/line

|              |     |
|--------------|-----|
| Cable length | 3 m |
|--------------|-----|


PVC gray [500]

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

|                                               |                                                                                                                            |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Dimensional drawing                           |                                          |
| Cable weight                                  | 231 kg/km                                                                                                                  |
| UL AWM Style                                  | 20233 / 10493 (80°C/300 V)                                                                                                 |
| Number of positions                           | 5                                                                                                                          |
| Shielded                                      | yes                                                                                                                        |
| Cable type                                    | PVC gray [500]                                                                                                             |
| Conductor structure, voltage supply           | 141x 0.15 mm                                                                                                               |
| AWG power supply                              | 14                                                                                                                         |
| Conductor cross-section                       | 5x 2.5 mm²                                                                                                                 |
| Wire diameter incl. insulation                | 3 mm ±0.1 mm                                                                                                               |
| External cable diameter                       | 10.80 mm ±0.3 mm                                                                                                           |
| Outer sheath, material                        | PVC                                                                                                                        |
| External sheath, color                        | gray RAL 7001                                                                                                              |
| Conductor material                            | Bare Cu litz wires                                                                                                         |
| Material wire insulation                      | PVC                                                                                                                        |
| Single wire, color                            | brown, white, blue, black, gray                                                                                            |
| Thickness, insulation                         | ≥ 0.36 mm                                                                                                                  |
| Thickness, outer sheath                       | approx. 0.76 mm                                                                                                            |
| Max. conductor resistance                     | ≤ 8 Ω/km (at 20 °C)                                                                                                        |
| Insulation resistance                         | ≥ 100 MΩ*km (at 20 °C)                                                                                                     |
| Nominal voltage, cable                        | ≤ 300 V AC                                                                                                                 |
| Test voltage                                  | ≥ 3000 V AC (Spark test)                                                                                                   |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                      |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                     |
| Smallest bending radius, fixed installation   | 54 mm                                                                                                                      |
| Smallest bending radius, movable installation | 108 mm                                                                                                                     |
| Dynamic load capacity (bending)               | Max. bending cycles: 1000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s² |
| Flame resistance                              | According to UL 758/1581 (Cable Flame)<br>according to UL 758/1581 FT1<br>According to DIN EN 60332-1-2                    |
| Resistance to oil                             | according to DIN EN 60811-404, 168 h at 60 °C                                                                              |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)<br>-20 °C ... 80 °C (Cable, flexible installation)                            |

## Environmental and real-life conditions

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

## Ambient conditions


|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
|                                                                   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-111 |


## Drawings

Dimensional drawing




M12 x 1 socket, angled

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

Diagram



Base curve


# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

Circuit diagram



Contact assignment of the M12 socket

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1414795>



**UL Listed**

Approval ID: E468743



**cUL Listed**

Approval ID: E468743



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060327 |
| ECLASS-15.0 | 27060327 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-5P- 3,0-500/M12FRL FE SH - Power cable



1414795

<https://www.phoenixcontact.com/nl/products/1414795>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 7,424 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)