

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PE-X halogen-free, black, shielded, Plug straight M12 SPEEDCON, coding: A, on free cable end, cable length: 5 m, For railway applications

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Securely locked by special vibration brake
- Resistant to temperature influences – tested for an extended temperature range and for resistance to temperature shocks
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1407326
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1CDA
Product key	AF1CDA
GTIN	4046356774420
Weight per piece (including packing)	365,1 g
Weight per piece (excluding packing)	379,1 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Technical data

Notes

General	Further products with variable cable type and variable cable length can be found in the accessories section
---------	---

Product properties

Application	Railway applications
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material of grip body	PA 6.6
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated
Standards/regulations	PA 6.6

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	5 m
--------------	-----

Shielded black RADOX® [28R]

Dimensional drawing		
Cable weight	70 kg/km	
Number of positions	5	
Shielded	yes	
Cable type	Shielded black RADOX® [28R]	
Conductor structure signal line	19x 0.18 mm	
AWG signal line	20	
Conductor cross-section	5x 0.5 mm²	
Wire diameter incl. insulation	1.43 mm	
External cable diameter	6.20 mm ±0.3 mm	
Outer sheath, material	PE-X	
External sheath, color	black	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	PE-X	
Single wire, color	white 1, white 2, white 3, white 4, white 5	
Overall twist	5 cores, twisted	
Max. conductor resistance	≤ 40.1 Ω/km	
Nominal voltage, cable	600 V AC (Core-ground, U ₀)	
	1000 V AC (Core-ground, U)	
	≤ 720 V AC (core-ground)	
	≤ 1200 V AC (Core-ground, U _m)	
	≤ 900 V DC (Core-ground, V ₀)	
Test voltage	≤ 1500 V DC (Line-line)	
	3500 V AC (50 Hz, 5 min.)	

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

	8400 V DC (50 Hz, 5 min.)
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	4 x D
Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	25 mm
Halogen-free	in accordance with EN 50267-2-1
Flame resistance	IEC 60332-1-2
	EN 50266
	EN 60332-3-25
	NF C32-070, 2.1
	NF C32-070, 2.2
	UL 1685, 12 (FT4)
	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Fume corrosiveness	EN 50267-2-2
Fume toxicity	BS 6853 B.1
	EN 50305, 9.2
Concentration of fumes	BS 6853 D.8.7
	EN 61034-2
	UL 1685, 12 (FT4)
Resistance to oil	according to IRM 902, 72 h at 100 °C
Fire protection in rail vehicles	BS 6853 (Category Ia, Ib, II)
	GM/RT 2130 (Category Ia, Ib, II)
	EN 45545 (Risk level HL1 - HL3)
	DIN 5510 (Fire protection level 1, 2, 3, 4)
	NF F16-101 (Category A1, A2, B)
	NF F16-101 (Class C/F0)
	NFPA 130
	UNI CEI 11170 (Risk level LR1 - LR4)
Other resistance	Resistance to fuels (according to IRM 903, 168 h at 70 °C)
Ambient temperature (operation)	-50 °C ... 120 °C (cable, fixed installation)
	-25 °C ... 90 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standard designation	Shock, vibration

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Standards/specifications	EN 50155
--------------------------	----------


SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable

1407326

<https://www.phoenixcontact.com/nl/products/1407326>


Drawings

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Circuit diagram



Contact assignment of the M12 plug

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1407326>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-MS/ 5,0-28R SCO RAIL - Sensor/actuator cable



1407326

<https://www.phoenixcontact.com/nl/products/1407326>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	60579cba-a068-4362-b317-b723c6b95305

EF3.1 Climate Change

CO2e kg	2,703 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.

Hengelder 56 6902 PA Zevenaar

Postbus 246 6900 AE Zevenaar

(0316) 59 17 20

sales@phoenixcontact.nl