

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694

<https://www.phoenixcontact.com/nl/products/1444694>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Socket, straight, M12, A-coding, on free cable end, Individual wires, cable length: 2 m, 0.25 mm², potted, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1444694
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABQCHB
Product key	ABQCHB
GTIN	4046356567435
Weight per piece (including packing)	67,6 g
Weight per piece (excluding packing)	65,322 g
Customs tariff number	85444290
Country of origin	DE

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694

<https://www.phoenixcontact.com/nl/products/1444694>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
General	Contact connection method: Crimp connection

Mounting

Mounting type	Rear mounting (M16 x 1,5)
---------------	---------------------------

Product properties

Application	Signal
Number of positions	8
No. of cable outlets	1
Coding	A
Thread type	M12

Material specifications

Material Molding compound	PUR (potted)
---------------------------	--------------

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.25 mm ²

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	2 m
Cable cross section	0.25 mm ²
AWG signal line	24

Environmental and real-life conditions

Ambient conditions

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694

<https://www.phoenixcontact.com/nl/products/1444694>

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
UL Type Rating	Type 4 (indoor use only)

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694
<https://www.phoenixcontact.com/nl/products/1444694>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1444694>

	cULus Recognized Approval ID: E221474-20140616			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	24 - 22	-

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694

<https://www.phoenixcontact.com/nl/products/1444694>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12FS-8P-M16/2,0 - Device connector rear mounting



1444694

<https://www.phoenixcontact.com/nl/products/1444694>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2194853c-fa6d-4315-8e8a-1efbf5a50722

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl