

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, resistant to welding sparks, highly flexible, gray RAL 7001, free cable end, on Socket angled M12, coding: A, cable length: 10 m, for robots and drag chains

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Reliable solution for the body shop as cable is resistant to welding sparks

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1454299       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF1CBA        |
| Product key                          | AF1CBA        |
| GTIN                                 | 4046356576857 |
| Weight per piece (including packing) | 265,3 g       |
| Weight per piece (excluding packing) | 289,9 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

## Technical data

### Product properties

|                      |                        |
|----------------------|------------------------|
| Application          | Robots and drag chains |
| Number of positions  | 3                      |
| No. of cable outlets | 1                      |
| Shielded             | no                     |
| Coding               | A                      |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V AC                   |
|                       | 250 V DC                   |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>


## Connection 2

|                     |                   |
|---------------------|-------------------|
| Type                | Socket angled M12 |
| Number of positions | 3                 |
| Coding type         | A                 |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

## Gray, highly flexible PUR [800]

|                                               |                                                                                                  |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------|
| Dimensional drawing                           |                |
| Note                                          | Due to the extremely robust outer sheath, this cable should only be stripped in 5 cm increments. |
| Cable weight                                  | 28.3 kg/km                                                                                       |
| UL AWM Style                                  | 20549                                                                                            |
| Number of positions                           | 3                                                                                                |
| Shielded                                      | no                                                                                               |
| Cable type                                    | Gray, highly flexible PUR [800]                                                                  |
| Conductor structure signal line               | 42x 0.10 mm                                                                                      |
| AWG signal line                               | 22                                                                                               |
| Conductor cross-section                       | 3x 0.34 mm <sup>2</sup> (Signal line)                                                            |
| Wire diameter incl. insulation                | 1.3 mm ±0.05 mm (Signal line)                                                                    |
| External cable diameter                       | 4.50 mm ±0.2 mm                                                                                  |
| Outer sheath, material                        | PUR                                                                                              |
| External sheath, color                        | gray RAL 7001                                                                                    |
| Conductor material                            | Bare Cu litz wires                                                                               |
| Material wire insulation                      | PP                                                                                               |
| Single wire, color                            | brown, blue, black                                                                               |
| Overall twist                                 | 3 wires, twisted                                                                                 |
| Max. conductor resistance                     | approx. 53 Ω/km                                                                                  |
| Insulation resistance                         | ≥ 20 MΩ*km                                                                                       |
| Nominal voltage, cable                        | 300 V                                                                                            |
| Test voltage                                  | 2000 V                                                                                           |
| Minimum bending radius, fixed installation    | 4 x D                                                                                            |
| Minimum bending radius, flexible installation | 7.5 x D                                                                                          |
| Smallest bending radius, fixed installation   | 18 mm                                                                                            |
| Smallest bending radius, movable installation | 34 mm                                                                                            |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 7,5 x D,                                          |

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

|                                 |                                                                                                                                         |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
|                                 | Traversing path: 5 m, Traversing rate: 3.3 m/s, Acceleration: 5 m/s <sup>2</sup>                                                        |
|                                 | Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s <sup>2</sup> |
| Dynamic load capacity (torsion) | Torsion: $\pm 360$ °/m, Torsion cycles: 1000000, Torsional frequency: 35 cycles/min.                                                    |
| Halogen-free                    | in accordance with DIN VDE 0472 part 815                                                                                                |
| Flame resistance                | in accordance with UL 758/1581 FT2                                                                                                      |
| Resistance to oil               | in accordance with DIN EN 60811-2-1                                                                                                     |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents                                                                              |
| Special properties              | Silicone-free                                                                                                                           |
|                                 | Cable jacket is welding spark-resistant, recyclable, matt, low-adhesion, abrasion-resistant, flame-retardant, and self-extinguishing    |
|                                 | Free from silicone and cadmium                                                                                                          |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)                                                                                            |
|                                 | -25 °C ... 80 °C (Cable, flexible installation)                                                                                         |

## Environmental and real-life conditions

### Ambient conditions


|                                                                   |                                                 |
|-------------------------------------------------------------------|-------------------------------------------------|
| Degree of protection                                              | IP65                                            |
|                                                                   | IP67                                            |
|                                                                   | IP68                                            |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)                |
| Ambient temperature (operation) (Cable, fixed installation)       | -40 °C ... 90 °C (cable, fixed installation)    |
| Ambient temperature (operation) (Cable, flexible installation)    | -30 °C ... 90 °C (Cable, flexible installation) |
| Ambient temperature (operation)                                   | to 120 °C (for 3000 h)                          |
|                                                                   | to 90 °C (in acc. with UL)                      |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


## Drawings

Dimensional drawing




M12 x 1 socket, angled

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 socket

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1454299>



### UL Listed

Approval ID: FILE E 221474

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 300 V                 | 4 A                   | -                 | -                           |



### cUL Listed

Approval ID: FILE E 221474

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 300 V                 | 4 A                   | -                 | -                           |



### EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-3P-10,0-800/M12FR - Sensor/actuator cable



1454299

<https://www.phoenixcontact.com/nl/products/1454299>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1,402 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)