

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, INTERBUS (16 Mbps), 5-position, PUR halogen-free, may green RAL 6017, shielded, Plug straight M12 SPEEDCON, coding: B, on free cable end, cable length: 2 m

Commercial data

Item number	1517877
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1CKB
Product key	AF1CKB
GTIN	4017918967994
Weight per piece (including packing)	166,5 g
Weight per piece (excluding packing)	166,5 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Technical data

Product properties

Application	Standard
Sensor type	INTERBUS
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	B

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	INTERBUS
Signal type/category	INTERBUS, 16 Mbps

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC
	60 V DC
Nominal current I _N	4 A
Transmission medium	Copper
Transmission speed	16 Mbps

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Connection data

Connection assignment

Contact Color (signal designation) Contact (optional)	1 (Plug) YE (<u>DO</u>)
	2 (Plug) GN (<u>DO</u>)
	3 (Plug) GY (DI)
	4 (Plug) PK (<u>DI</u>)

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

5 (Plug) | BN (GND)

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	B (inverse)


Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	2 m
--------------	-----

INTERBUS [900]

Dimensional drawing	
Cable weight	70 kg/km
Number of positions	6
Shielded	yes
Cable type	INTERBUS [900]
Conductor structure	3 x 2 x 0.22 mm ²
Signal speed	0.66 c
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	3x 2x 0.22 mm ²
External cable diameter	8.00 mm
Outer sheath, material	PUR
External sheath, color	may green RAL 6017
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	green-yellow, white-brown, gray-pink
Twisted pairs	2 cores to the pair
Overall twist	3 pairs to the core
Insulation resistance	≥ 5 GΩ*km
Coupling resistance	< 250.00 mΩ/m (at 30 MHz)
Loop resistance	≤ 159.80 Ω/km

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable




1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Wave impedance	120 Ω $\pm$ 20 % (at 64 kHz)
	100 Ω $\pm$ 15 % (with 1 MHz)
Cable capacity	$\leq$ 60 nF/km (At 800 Hz)
Nominal voltage, cable	250 V (Peak value, not for high-power applications)
Test voltage Core/Core	1500 V _{rms}
Test voltage Core/Shield	1000.00 V _{rms}
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	15 x D
Smallest bending radius, fixed installation	60 mm
Smallest bending radius, movable installation	120 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 120 mm, Traversing path: 10 m, Traversing rate: 1.6 m/s, Acceleration: 3.2 m/s ²
Near end crosstalk attenuation (NEXT)	$\geq$ 61 dB (at 772 kHz)
	$\geq$ 59 dB (with 1 MHz)
	$\geq$ 55 dB (at 2 MHz)
	$\geq$ 50 dB (at 4 MHz)
	$\geq$ 46 dB (at 8 MHz)
	$\geq$ 44 dB (at 10 MHz)
	$\geq$ 41 dB (at 16 MHz)
Shield attenuation	$\geq$ 40 dB (at 20 MHz)
	$\leq$ 15 dB/km (at 256 kHz)
	$\leq$ 24 dB/km (at 772 kHz)
	$\leq$ 27 dB/km (with 1 MHz)
	$\leq$ 52 dB/km (at 4 MHz)
	$\leq$ 84 dB/km (at 10 MHz)
	$\leq$ 112 dB/km (at 16 MHz)
Flame resistance	$\leq$ 119 dB/km (at 20 MHz)
	according to VDE 0472, Part 4, test type B
Ambient temperature (operation)	according to IEC 60332-1
	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)


Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

Circuit diagram



Contact assignment of the M12 plug

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1517877>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/nl/products/1517877>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0,868 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl