

RC-16P1N1280K5 - Cable connector



1600595

<https://www.phoenixcontact.com/nl/products/1600595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, straight, Screw locking mechanism, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1600595
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	ABRAAA
Product key	ABRAFA
GTIN	4046356230926
Weight per piece (including packing)	73,985 g
Weight per piece (excluding packing)	70,243 g
Customs tariff number	85366990
Country of origin	DE

RC-16P1N1280K5 - Cable connector



1600595

<https://www.phoenixcontact.com/nl/products/1600595>

Technical data

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Number Contact (Contact group 1)	16
Diameter Contact (Contact group 1)	1 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65
	IP67
	IP68

RC-16P1N1280K5 - Cable connector


1600595

<https://www.phoenixcontact.com/nl/products/1600595>



Drawings

Schematic diagram



Connector pin assignment


RC-16P1N1280K5 - Cable connector

1600595

<https://www.phoenixcontact.com/nl/products/1600595>



Schematic diagram



Dimensional drawing

RC-16P1N1280K5 - Cable connector



1600595

<https://www.phoenixcontact.com/nl/products/1600595>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-16P1N1280K5 - Cable connector



1600595

<https://www.phoenixcontact.com/nl/products/1600595>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7ea88f1d-dc58-4db0-8a26-3361282c276d

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl