

CA-17F1N8A85DUS - Cable connector



1619470
<https://www.phoenixcontact.com/nl/products/1619470>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629204

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1619470
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABRAEB
Product key	ABRAEB
GTIN	4046356823777
Weight per piece (including packing)	94,2 g
Weight per piece (excluding packing)	89,934 g
Customs tariff number	85366990
Country of origin	DE

CA-17F1N8A85DUS - Cable connector



1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Technical data

Notes

Order information:	Order 17 x 1 mm crimp contacts separately
Order information:	When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786600)

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Feedback, signal
	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number Contact (Signal contacts)	17
Diameter Contact (Signal contacts)	1 mm
Litz wire cross-section min. Contact (Signal contacts)	0.06 mm ²
Litz wire cross-section max. Contact (Signal contacts)	1 mm ²
Rated current Contact (Signal contacts)	8 A (for max. connection cross section)
Rated voltage Contact (Signal contacts)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	SPEEDCON
Pg screw connection	none
Housing material	Metal
Degree of protection (plugged in)	IP67

Seal

External cable diameter	3 mm ... 14.5 mm
-------------------------	------------------

CA-17F1N8A85DUS - Cable connector



1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Seal material	FPM
---------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-17F1N8A85DUS - Cable connector




1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

CA-17F1N8A85DUS - Cable connector



1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1619470>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	48 V	5 A	18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	48 V	8 A	18	-

CA-17F1N8A85DUS - Cable connector



1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-17F1N8A85DUS - Cable connector



1619470

<https://www.phoenixcontact.com/nl/products/1619470>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl