

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 6 mm ... 10 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1341234

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1619661
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABRAEA
Product key	ABRAEA
GTIN	4046356822176
Weight per piece (including packing)	95,2 g
Weight per piece (excluding packing)	88,957 g
Customs tariff number	85366990
Country of origin	DE

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Technical data

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Number Contact (Power contacts)	3
Diameter Contact (Power contacts)	1.5 mm
Litz wire cross-section min. Contact (Power contacts)	0.08 mm ²
Litz wire cross-section max. Contact (Power contacts)	1 mm ²
Rated current Contact (Power contacts)	10 A
Rated voltage Contact (Power contacts)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Signal contacts)	16
Diameter Contact (Signal contacts)	1 mm
Litz wire cross-section min. Contact (Signal contacts)	0.08 mm ²
Litz wire cross-section max. Contact (Signal contacts)	1 mm ²
Rated current Contact (Signal contacts)	8 A

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Seal

External cable diameter	6 mm ... 10 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


CA-19S1N128007 - Cable connector

1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Drawings

Schematic diagram



Connector pin assignment

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1619661>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Power	48 V	6 A	18	-
Signal	48 V	5 A	18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Power	48 V	10 A	18	-
Signal	48 V	8 A	18	-

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-19S1N128007 - Cable connector



1619661

<https://www.phoenixcontact.com/nl/products/1619661>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d6b8bc2a-adb6-4e92-ab44-ee9ca69a1261

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl