

# CA-09P1N8A8008 - Cable connector



1619648  
<https://www.phoenixcontact.com/nl/products/1619648>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 6-pos.  
product version with solder  
contacts

M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 10 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629217

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1619648                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | ABRAEA                         |
| Product key                          | ABRAEA                         |
| GTIN                                 | 4046356822305                  |
| Weight per piece (including packing) | 92,5 g                         |
| Weight per piece (excluding packing) | 84,387 g                       |
| Customs tariff number                | 85366990                       |
| Country of origin                    | DE                             |

# CA-09P1N8A8008 - Cable connector



1619648

<https://www.phoenixcontact.com/nl/products/1619648>

## Technical data

### Notes

|                    |                                                        |
|--------------------|--------------------------------------------------------|
| Order information: | Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately |
|--------------------|--------------------------------------------------------|

### Connector

#### Insulating body

|                                                        |                                                                           |
|--------------------------------------------------------|---------------------------------------------------------------------------|
| Note                                                   | Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately |
| Coding                                                 | N                                                                         |
| Material (Insulating body)                             | PA 6.6                                                                    |
| Connection method                                      | Crimp connection                                                          |
| Contact switching type                                 | Pin                                                                       |
| Application                                            | Signal                                                                    |
| Number of positions                                    | 9                                                                         |
| Direction of rotation                                  | Standard                                                                  |
| Connection profile                                     | 8+1                                                                       |
| Number Contact (Contact group 1)                       | 1                                                                         |
| Diameter Contact (Contact group 1)                     | 2 mm                                                                      |
| Litz wire cross-section min. Contact (Contact group 1) | 1 mm <sup>2</sup>                                                         |
| Litz wire cross-section max. Contact (Contact group 1) | 2.5 mm <sup>2</sup>                                                       |
| Rated current Contact (Contact group 1)                | 20 A                                                                      |
| Rated voltage Contact (Contact group 1)                | 48 V AC<br>74 V DC                                                        |
| Rated surge voltage                                    | 1.5 kV                                                                    |
| Overvoltage category                                   | III                                                                       |
| Degree of pollution                                    | 3                                                                         |
| Number Contact (Contact group 2)                       | 8                                                                         |
| Diameter Contact (Contact group 2)                     | 1 mm                                                                      |
| Litz wire cross-section min. Contact (Contact group 2) | 0.08 mm <sup>2</sup>                                                      |
| Litz wire cross-section max. Contact (Contact group 2) | 1 mm <sup>2</sup>                                                         |
| Rated current Contact (Contact group 2)                | 8 A                                                                       |

#### Housing

|                                   |                                                                      |
|-----------------------------------|----------------------------------------------------------------------|
| Type                              | Cable connector housing                                              |
| Thread type                       | M23                                                                  |
| Design                            | straight                                                             |
| Type of locking                   | Screw locking mechanism                                              |
| Pg screw connection               | none                                                                 |
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Material for screw connection     | CuZn                                                                 |
| Degree of protection (plugged in) | IP67                                                                 |

# CA-09P1N8A8008 - Cable connector



1619648

<https://www.phoenixcontact.com/nl/products/1619648>

## Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material           | NBR               |

## Environmental and real-life conditions

### Ambient conditions

|                                          |                   |
|------------------------------------------|-------------------|
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |

# CA-09P1N8A8008 - Cable connector


1619648

<https://www.phoenixcontact.com/nl/products/1619648>



## Drawings

Schematic diagram



Connector pin assignment

# CA-09P1N8A8008 - Cable connector



1619648

<https://www.phoenixcontact.com/nl/products/1619648>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1619648>

|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                    |                       |                       |                   |                             |
| Power                                                                                                                                    | 48 V                  | 12 A                  | 14                | -                           |
| Signal                                                                                                                                   | 48 V                  | 4 A                   | 20                | -                           |

|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                   |                       |                       |                   |                             |
| Power                                                                                                                                   | 48 V                  | 20 A                  | 14                | -                           |
| Signal                                                                                                                                  | 48 V                  | 6 A                   | 20                | -                           |

# CA-09P1N8A8008 - Cable connector



1619648

<https://www.phoenixcontact.com/nl/products/1619648>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-09P1N8A8008 - Cable connector



1619648

<https://www.phoenixcontact.com/nl/products/1619648>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | efa0ff2a-684a-4c6c-bcb1-db6107af4bbc |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)