

CA-12P1NA22S00 - Device connector front mounting



1619924

<https://www.phoenixcontact.com/nl/products/1619924>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder-in connection, Flat gasket, flange dimensions: 25 mm x 25 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Your advantages

- Safe use in the field, thanks to high degree of protection
- Consistent EMC protection for reliable transmission of signals
- Easy device integration: solder-in contacts available in different lengths

Commercial data

Item number	1619924
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABRAEL
Product key	ABRAEL
GTIN	4046356820462
Weight per piece (including packing)	31,9 g
Weight per piece (excluding packing)	25,339 g
Customs tariff number	85366990
Country of origin	DE

CA-12P1NA22S00 - Device connector front mounting



1619924

<https://www.phoenixcontact.com/nl/products/1619924>

Technical data

Dimensions

Length of the solder pin	10 mm
	10 mm

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Connection method	Solder-in connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	12
Diameter Contact (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing


Type	Flange housing
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Mounting type	Front mounting/square flange (4x Ø 3.2 mm)
Flange dimensions	25 mm x 25 mm
Material (Housing)	GD-Zn
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Drawings



Dimensional drawing

Schematic diagram



Connector pin assignment

Technical drawing of a mechanical part, likely a flange or a similar component, showing dimensions in millimeters. The drawing includes a central circular feature with a grid of holes and a surrounding rectangular flange. Dimensions are provided for various features:

- Overall width: 11,1
- Overall height: 9,8
- Central hole diameter: 7,2
- Distance from top edge to center of first hole: 5,3
- Distance between first and second holes: 2,8
- Distance between second and third holes: 2,2
- Distance from bottom edge to center of first hole: 3,8
- Distance from center of first hole to center of second hole: 4,3
- Distance from center of second hole to center of third hole: 4,5

Mar 4, 2026, 6:22 PM Page 5 (8)

CA-12P1NA22S00 - Device connector front mounting



1619924

<https://www.phoenixcontact.com/nl/products/1619924>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1619924>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	48 V	6 A	18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	48 V	8 A	18	-

CA-12P1NA22S00 - Device connector front mounting



1619924

<https://www.phoenixcontact.com/nl/products/1619924>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 10.0	EC003569
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d30947a6-5689-4484-b5d1-71894ee51558