

TGGM/CDIO/17-ST - Cable connector



1667895

<https://www.phoenixcontact.com/nl/products/1667895>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version without external cable gland

M23, Cable connector, series: UC, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1667895
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABRAIA
Product key	ABRAIA
GTIN	4017918163617
Weight per piece (including packing)	148 g
Weight per piece (excluding packing)	141,338 g
Customs tariff number	85366990
Country of origin	DE

1667895

<https://www.phoenixcontact.com/nl/products/1667895>

Technical data

Product properties

Number of positions	17
---------------------	----

Material specifications

Seal material	NBR
---------------	-----

Connector

Insulating body

Note	Assembly note Integrated contacts: 17 x 1597862
Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number Contact (Contact group 1)	17
Diameter Contact (Contact group 1)	1 mm
Litz wire cross-section min. Contact (Contact group 1)	0.14 mm²
Litz wire cross-section max. Contact (Contact group 1)	0.56 mm²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Type of locking	Screw locking mechanism
Pg screw connection	Pg16
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

TGGM/CDIO/17-ST - Cable connector



1667895

<https://www.phoenixcontact.com/nl/products/1667895>


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C (short-term up to 145°C)

Drawings

Schematic diagram




Connector pin assignment


1667895

<https://www.phoenixcontact.com/nl/products/1667895>

Schematic diagram



Dimensional drawing



TGGM/CDIO/17-ST - Cable connector



1667895

<https://www.phoenixcontact.com/nl/products/1667895>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	84ce6893-36ab-462d-91b0-849d417d3fd8