

# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection, consisting of protective plug and base element, with integrated status indicator for a 2-wire floating signal circuit. Can be used in safety-related circuits up to SIL 3.

## Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Continuous monitoring of protective devices, plus mechanical status indicator with optional remote signaling
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features
- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2908193       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL2162        |
| Product key                          | CL2162        |
| GTIN                                 | 4055626282688 |
| Weight per piece (including packing) | 41,125 g      |
| Weight per piece (excluding packing) | 34,59 g       |
| Customs tariff number                | 85363010      |
| Country of origin                    | DE            |

# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Technical data

### Product properties

|                         |                                         |
|-------------------------|-----------------------------------------|
| Product family          | TERMITRAB complete                      |
| IEC test classification | C1                                      |
|                         | C2                                      |
|                         | C3                                      |
|                         | D1                                      |
| Type                    | DIN rail module, two-section, divisible |
| Wire pairs per module   | 1                                       |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |


### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 12 V DC |
|-----------------------|---------|

### Connection data

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection method                | Push-in connection                          |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section AWG      | 24 ... 12                                   |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 6.2 mm +0.1 mm                                                                       |
| Height              | 105.8 mm                                                                             |
| Depth               | 100 mm (incl. DIN rail 7.5 mm)                                                       |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color (Base element)                   | gray (RAL 7042)       |
| Color (Male connector)                 | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V-0                   |
| Insulating material                    | PBT                   |
| Housing material                       | PBT                   |

### Mechanical properties

#### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Protective circuit

|                                                                 |                                                                                    |
|-----------------------------------------------------------------|------------------------------------------------------------------------------------|
| Direction of action                                             | Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground |
| Nominal voltage $U_N$                                           | 12 V DC                                                                            |
| Maximum continuous operating voltage $U_C$                      | 15 V DC                                                                            |
|                                                                 | 10 V AC                                                                            |
| Rated current                                                   | 600 mA (56 °C)                                                                     |
| Operating effective current $I_C$ at $U_C$                      | $\leq 100 \mu A$                                                                   |
| Protective conductor current $I_{PE}$                           | $\leq 1 \mu A$                                                                     |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (line-line)      | 5 kA                                                                               |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (line-ground)    | 5 kA                                                                               |
| Pulse discharge current $I_{imp}$ (10/350) $\mu s$ (line-line)  | 0.5 kA                                                                             |
| Pulse discharge current $I_{imp}$ (10/350) $\mu s$ (line-earth) | 0.5 kA                                                                             |
| Total discharge current $I_{Total}$ (8/20) $\mu s$              | 10 kA                                                                              |
| Voltage protection level $U_p$ (line-line)                      | $\leq 220 V$ (C1 - 1 kV / 500 A)                                                   |
|                                                                 | $\leq 350 V$ (C2 - 10 kV / 5 kA)                                                   |
|                                                                 | $\leq 25 V$ (C3 - 25 A)                                                            |
|                                                                 | $\leq 35 V$ (C3 - 100 A)                                                           |
| Voltage protection level $U_p$ (line-earth)                     | $\leq 750 V$ (C1 - 1 kV / 500 A)                                                   |
|                                                                 | $\leq 750 V$ (C2 - 10 kV / 5 kA)                                                   |
|                                                                 | $\leq 700 V$ (C3 - 25 A)                                                           |
|                                                                 | $\leq 750 V$ (C3 - 100 A)                                                          |
| Voltage protection level $U_p$ static (line-line)               | $\leq 30 V$ (C1 - 1 kV / 500 A)                                                    |
|                                                                 | $\leq 81 V$ (C2 - 10 kV / 5 kA)                                                    |
| Voltage protection level $U_p$ static (line-earth)              | $\leq 750 V$ (C1 - 1 kV / 500 A)                                                   |
|                                                                 | $\leq 750 V$ (C2 - 10 kV / 5 kA)                                                   |
| Response time $t_A$ (line-line)                                 | $\leq 1 ns$                                                                        |
| Response time $t_A$ (line-earth)                                | $\leq 100 ns$                                                                      |
| Input attenuation aE, sym.                                      | typ. 0.3 dB ( $\leq 130 kHz/150 \Omega$ )                                          |
| Cut-off frequency $f_g$ (3 dB), sym. in 150 $\Omega$ system     | typ. 420 kHz                                                                       |
| Capacity (Core-Core)                                            | typ. 5.2 nF                                                                        |
| Resistance per path                                             | 1.65 $\Omega \pm 20 \%$                                                            |
| Surge protection fault message                                  | optical                                                                            |
| Max. required back-up fuse                                      | 630 mA (FF)                                                                        |
| Impulse durability (line-line)                                  | C1 - 1 kV / 500 A                                                                  |
|                                                                 | C2 - 10 kV / 5 kA                                                                  |
|                                                                 | C3 - 100 A                                                                         |
| Impulse durability (line-earth)                                 | C1 - 1 kV / 500 A                                                                  |
|                                                                 | C2 - 10 kV / 5 kA                                                                  |
|                                                                 | C3 - 100 A                                                                         |
|                                                                 | D1 - 500 A                                                                         |
| Pulse reset time (line-line)                                    | $\leq 700 ms$                                                                      |
| Pulse reset time (line-earth)                                   | $\leq 1500 ms$                                                                     |

# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Additional technical data

|                                                                        |            |
|------------------------------------------------------------------------|------------|
| Max. total discharge current $I_{\text{total max}} (8/20) \mu\text{s}$ | 20 kA (1x) |
|------------------------------------------------------------------------|------------|

## Environmental and real-life conditions

### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Degree of protection                    | IP20             |
| Ambient temperature (operation)         | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude                                | ≤ 4000 m (amsl)  |
| Permissible humidity (operation)        | 5 % ... 95 %     |

## Standards and regulations

|                          |                                                       |
|--------------------------|-------------------------------------------------------|
| Standards/specifications | IEC 61643-21                                          |
| Note                     | 2000 + corrigendum 2001 + A1:2008, modified + A2:2012 |

### EN 61643-21

|                          |                          |
|--------------------------|--------------------------|
| Standards/specifications | EN 61643-21              |
| Note                     | 2001 + A1:2009 + A2:2013 |

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | DIN rail: TH 35 - 7.5 mm |
|---------------|--------------------------|


TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193  
<https://www.phoenixcontact.com/nl/products/2908193>

Drawings

Dimensional drawing




Schematic diagram

| TTC-6P-1x2-...-I                                                                                                                                                                 |                          |                           |                          |       |                          |                            |      |                          |       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|---------------------------|--------------------------|-------|--------------------------|----------------------------|------|--------------------------|-------|
| Category                                                                                                                                                                         | 1oo1 architecture, HFT=0 |                           |                          |       | 1oo2 architecture, HFT=1 |                            |      |                          |       |
|                                                                                                                                                                                  | PFD <sub>AVG</sub>       | PFH                       | Used budget of SIL 2 SIF |       | PFD <sub>AVG</sub>       | PFH                        | CCF  | Used budget of SIL 3 SIF |       |
|                                                                                                                                                                                  |                          |                           | PFD <sub>AVG</sub>       | PFH   |                          |                            |      | PFD <sub>AVG</sub>       | PFH   |
|                                                                                                                                                                                  |                          |                           |                          |       |                          |                            |      |                          |       |
|                                                                                                                                                                                  | 3.88·10 <sup>-5</sup>    | 6.90·10 <sup>-9</sup> 1/h | 0.4 %                    | 0.7 % | 1.94·10 <sup>-6</sup>    | 3.45·10 <sup>-10</sup> 1/h | 5 %  | 0.2 %                    | 0.3 % |
|                                                                                                                                                                                  |                          |                           |                          |       | 3.88·10 <sup>-6</sup>    | 6.90·10 <sup>-10</sup> 1/h | 10 % | 0.4 %                    | 0.7 % |
| Calculation based on exida report, Phoenix Contact 16/06-072 R022 V4R2<br>exida Profile 1, FMEDA Analysis 2, T <sub>proof</sub> : 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99% |                          |                           |                          |       |                          |                            |      |                          |       |
| Used standards<br>IEC/EN 61508, edition 2010 (device specific)<br>IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific)                                             |                          |                           |                          |       |                          |                            |      |                          |       |

Functional safety scenarios

Diagram




# TTC-6P-1X2-12DC-PT-I - Surge protection device

2908193

<https://www.phoenixcontact.com/nl/products/2908193>



Circuit diagram



# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2908193>



**CSA**

Approval ID: 70136717



**DNV GL**

Approval ID: TAE000027G



**UL Listed**

Approval ID: FILE E 138168



**CSAus**

Approval ID: 70136717

**UAE-RoHS**

Approval ID: 22-06-16192

**Functional Safety**

Approval ID: 16-06-072 R022 V4R3

# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171501 |
| ECLASS-15.0 | 27171501 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000943 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|



# TTC-6P-1X2-12DC-PT-I - Surge protection device



2908193

<https://www.phoenixcontact.com/nl/products/2908193>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | b9cf7c46-4878-4988-8565-1dd631590d6d |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)