

FA MCR-EX-DS-I-I-OLP - Digital display



2908800

<https://www.phoenixcontact.com/nl/products/2908800>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ex i, Output loop-powered process indicator for installation in the control cabinet. HART



Commercial data

Item number	2908800
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DK1241
Product key	DK1241
GTIN	4055626357225
Weight per piece (including packing)	367,3 g
Weight per piece (excluding packing)	353,5 g
Customs tariff number	85437090
Country of origin	DE

Technical data

Product properties

Product family	Field Analog
Configuration	Keyboard
	Software

System properties

Functionality

Configuration	Keyboard
	Software

Electrical properties

Maximum temperature coefficient	< 0.02 %/K
Maximum transmission error	0.1 % (of final value)

Supply

Supply voltage range	loop-powered, no external supply necessary
----------------------	--

Input data

Signal: Current

Current input signal	4 mA ... 20 mA
Max. current input signal	200 mA
Voltage drop	≤ 1 V
	≤ 3.9 V (with display lighting)
Input impedance	≈ $\oplus \downarrow \Omega$

Signal: HART

Current input signal	up to 4x HART process variables
Voltage drop	≤ 1.9 V
	≤ 4.8 V (with display lighting)
Input impedance	$R_x = 40 \Omega / C_x = 2.3 \text{ nF}$

Output data

Signal: Current

Current output signal	4 mA ... 20 mA
Number of positions displayed	5
Display	7-segment LC display, with backlight, dot matrix for text/bar graph
Display value	scalable

Signal: HART

Current output signal	up to 4x HART process variables
-----------------------	---------------------------------

Connection data

Connection method	Push-in connection
Stripping length	9 mm
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 16

Ex data

Ex installation (EPL)	Gb
	Div. 1
Ex i circuits (EPL)	Gb
	Div. 1

Interfaces

Data communication (bypass)

Protocols supported	HART
---------------------	------

Dimensions

Width	96 mm
Height	48 mm
Depth	41.5 mm

Material specifications

Color	light gray (RAL 7035)
Housing material	Aluminum / polycarbonate

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (Front)
	IP20 (On the rear)
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	< 5000 m (Above sea level)
Climatic class	according to IEC 60654-1, class B2

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	Ⓔ II 2G Ex ib IIC T6 Gb
Certificate	PTB 17 ATEX 2025 X

FA MCR-EX-DS-I-I-OLP - Digital display



2908800

<https://www.phoenixcontact.com/nl/products/2908800>

IECEX

Identification	Ex ib IIC T6 Gb
Certificate	IECEX PTB 16.0033X

UKCA Ex (UKEX)

Certificate	CML 21UKEX2993X
-------------	-----------------

CCC / China-Ex

Identification	Ex ib IIC T6 Gb
Certificate	2021322309004298

UL, USA/Canada

Identification	UL 61010 Listed
----------------	-----------------

Shipbuilding approval

Certificate	DNV GL TAA000013C
-------------	-------------------

Shipbuilding data

Temperature	B
Humidity	B
Vibration	A
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

EMC data

Noise emission

Standards/regulations	IEC 61326, class B
-----------------------	--------------------

Standards and regulations

GB Standard


Standards/regulations	GB 3836.1
	GB 3836.4

Mounting

Mounting type	Panel mount
Mounting position	Max. viewing angle range +/- 45° from the centre line of the display in every direction

Drawings

Block diagram



Block diagram FA MCR-EX-DS-I-I-OLP

FA MCR-EX-DS-I-I-OLP - Digital display



2908800

<https://www.phoenixcontact.com/nl/products/2908800>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2908800>



EAC

Approval ID: RU*DE.*08.B.01522/19



UL Listed

Approval ID: E330267



cUL Listed

Approval ID: FILE E 330267



CCC

Approval ID: 2021322309004298

DNV

Approval ID: TAA000013C



IECEx

Approval ID: IECEx PTB 16.0033X



ATEX

Approval ID: PTB 17 ATEX 2025 X



CSA

Approval ID: 70106894



FM approved

Approval ID: FM16US0464



CSAus

Approval ID: 70106894

FA MCR-EX-DS-I-I-OLP - Digital display



2908800

<https://www.phoenixcontact.com/nl/products/2908800>

Classifications

ECLASS

ECLASS-13.0	27210301
ECLASS-15.0	27210301

ETIM

ETIM 9.0	EC011349
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------