

Cable - CABLE-D- 9SUB/M/OE/0,25/S/1,0M - 2926373

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled shielded round cable; connection 1: Single wires (9-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB pin strip (1x 9-position); cable length: 1 m

Why buy this product

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Connector according to IEC 60807-2/DIN 41652
- D-SUB socket or pin strip at one end
- 1:1 connection
- Shield connection: H05V-K 1 mm² cable, black, 0.5 m in length
- Screw connection: 2 UNC 4-40 screws
- Open end at one end

Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4046356548144

Technical data

General

Nominal voltage U _N	25 V AC
	60 V DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	≤ 0.09 Ω/m
Length of cable	1 m
Single wire, cross section	0.25 mm ²
Single wire, cross section [AWG]	24
External diameter	7.5 mm

Cable - CABLE-D- 9SUB/M/OE/0,25/S/1,0M - 2926373

Technical data

General

Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

Connector 1

Connection name	Field level
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	9

Connector 2

Connection name	Controller level
Connection method	Single wires
Number of positions	9
Note	The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.

Supported controller

Controller	universal
------------	-----------

Color code

Connector 1 = connector 2 (optional) = wire color	D-SUB 9 (1) = white
	D-SUB 9 (2) = brown
	D-SUB 9 (3) = green
	D-SUB 9 (4) = yellow
	D-SUB 9 (5) = gray
	D-SUB15 (6) = pink
	D-SUB 9 (7) = blue
	D-SUB 9 (8) = red
	D-SUB 9 (9) = black

Standards and Regulations

Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1
Connection in acc. with standard	CUL

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	--

Cable - CABLE-D- 9SUB/M/OE/0,25/S/1,0M - 2926373

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Approvals


Approvals


Approvals


UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized


Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN	125 V		
Nominal current IN	2 A		

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN	125 V		
Nominal current IN	2 A		

CSA		http://www.csagroup.org/services-industries/product-listing/	70002966
Nominal voltage UN	125 V		
Nominal current IN	1 A		

EAC		RU C- DE.A*30.B00767	
-----	---	-------------------------	--

Cable - CABLE-D- 9SUB/M/OE/0,25/S/1,0M - 2926373

Approvals

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>