

VIP-3/PT/PDM-2/16 - Potential distributors



2903797

<https://www.phoenixcontact.com/nl/products/2903797>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35 rails. Module width: 41.9 mm

Commercial data

Item number	2903797
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DK2124
Product key	DK2124
GTIN	4046356796712
Weight per piece (including packing)	104,6 g
Weight per piece (excluding packing)	121,2 g
Customs tariff number	85369010
Country of origin	US

Technical data

Notes

Type of insulation housing	Polyamide PA non-reinforced
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Product properties

Product family	VARIOFACE Professional
Potential connections	Per potential (P1, P2) 2 power/8 distributor terminal blocks

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	250 V AC/DC
Max. current carrying capacity per branch	15 A
Max. total current of all branches	30 A (per potential)

Input data

Potential connections	Per potential (P1, P2) 2 power/8 distributor terminal blocks
-----------------------	--

Connection data

Feed-in

Connection method	Push-in connection
Stripping length	15 mm
Number of connections	2
Conductor cross-section rigid	0.25 mm ² ... 6 mm ²
Conductor cross-section flexible	0.25 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 10

Distribution

Connection method	Push-in connection
Stripping length	8 mm
Number of connections	8
Number of positions	2
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Dimensions


VIP-3/PT/PDM-2/16 - Potential distributors



2903797

<https://www.phoenixcontact.com/nl/products/2903797>

Dimensional drawing



Width	41.9 mm
Height	75.8 mm
Depth	63 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C (NOTE: At maximum relative humidity < 90%.)
Ambient temperature (storage/transport)	-20 °C ... 70 °C (NOTE: At maximum relative humidity < 90%.)
Altitude	< 2000 m
Permissible humidity (operation)	90 %
Permissible humidity (storage/transport)	90 %

Standards and regulations


Standards/regulations	EN IEC 61010-2-201
-----------------------	--------------------

Mounting


Mounting type	DIN rail mounting
Mounting position	any

Drawings

Dimensional drawing



Circuit diagram



VIP-3/PT/PDM-2/16 - Potential distributors



2903797

<https://www.phoenixcontact.com/nl/products/2903797>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2903797>



CSA

Approval ID: 2122203



cUL Recognized

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Output	250 V	15 A	26 - 14	-
Input	250 V	15 A	24 - 8	-



UL Recognized

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Output	250 V	15 A	26 - 14	-
Input	250 V	15 A	24 - 8	-

VIP-3/PT/PDM-2/16 - Potential distributors



2903797

<https://www.phoenixcontact.com/nl/products/2903797>

Classifications

ECLASS

ECLASS-13.0	27400609
ECLASS-15.0	27400609

ETIM

ETIM 10.0	EC001894
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/PT/PDM-2/16 - Potential distributors



2903797

<https://www.phoenixcontact.com/nl/products/2903797>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl