


STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation protective conductor terminal block, nom. voltage: 24 V, nominal current: 18 A, number of connections: 4, connection method: Spring-cage connection, Rated cross section: 2.5 mm², cross section: 0.08 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Three-conductor output terminal block of the same shape with PE connection in the lower level for wiring actuators
- Power terminal blocks can be located at any point on the terminal strip for supply or extension purposes
- Easy bridging and potential distribution using the patented plug-in bridges from the CLIPLINE complete system
- Versions with LED for indicating the switching states
- For space and time-saving wiring of three-conductor initiators and actuators
- Potential is supplied via the STIO-IN power terminal blocks
- The upper level is for signal wiring, whereas the two lower levels are used to distribute the positive and negative potential

Commercial data

Item number	3209141
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE2117
Product key	BE2117
GTIN	4046356143509
Weight per piece (including packing)	11,77 g
Weight per piece (excluding packing)	11,77 g
Customs tariff number	85369010
Country of origin	TR

STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Technical data

Product properties

Number of connections	4
Number of rows	3

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	0.77 W
LED voltage range	15 V DC ... 30 V DC
LED current range	1 mA ... 2.5 mA

Input data

LED voltage range	15 V DC ... 30 V DC
-------------------	---------------------

Connection data

Grounding foot	Yes
Number of connections per level	2
Nominal cross section	2.5 mm ²
Connection method	Spring-cage connection
Note	Please observe the current carrying capacity of the DIN rails.
Stripping length	8 mm ... 10 mm
Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
Conductor cross-section rigid	0.08 mm ² ... 4 mm ²
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	28 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal cross section	2.5 mm ²
Nominal current	18 A
Maximum load current	18 A (with 4 mm ² conductor cross-section)
Nominal voltage	24 V (Light indicator, green)

Dimensions

Width	5.2 mm
End cover width	2.2 mm

STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Height	75 mm
Depth on NS 35/7,5	44.5 mm
Depth on NS 35/15	52 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
----------------------------------	-----------------------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15


STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block

3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Drawings

Circuit diagram



STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/3209141>



EAC

Approval ID: RU C-DE.BL08.B.00644



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	10 A	28 - 12	-
C				
	150 V	18 A	28 - 12	-
D				
	300 V	10 A	28 - 12	-



EAC

Approval ID: KZ7500651131219505

STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Classifications

ECLASS

ECLASS-13.0	27250112
ECLASS-15.0	27250112

ETIM

ETIM 10.0	EC000900
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STIO 2,5/3-PE/B/L-LA24GN/O-M - Installation protective conductor terminal block



3209141

<https://www.phoenixcontact.com/nl/products/3209141>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
SCIP	8407e211-0335-4a17-aa87-d8f7ba0bc7fd

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl