

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



UL Recognized type 1 SPD and IEC type 2 surge protection plug with a varistor and thermal disconnect for use with VAL-US base elements, mechanical and visual fault warning

## Product description

Surge protective device replacement plug

## Your advantages

- Thermal disconnect device for each individual plug
- Optical, mechanical status indication for the individual arresters
- Pluggable
- Mechanical coding of all slots
- Consists of base element and plug

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2910338       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL1321        |
| Product key                          | CL1321        |
| GTIN                                 | 4055626444802 |
| Weight per piece (including packing) | 51,8 g        |
| Weight per piece (excluding packing) | 46 g          |
| Customs tariff number                | 85363030      |
| Country of origin                    | DE            |

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

## Technical data

### Notes

|         |          |
|---------|----------|
| General | Used in: |
|---------|----------|

### Product properties

|                                |              |
|--------------------------------|--------------|
| Product family                 | VALVETRAB MS |
| IEC test classification        | II           |
|                                | T2           |
| EN type                        | T2           |
| Type                           | Male         |
| Number of positions            | 1            |
| Surge protection fault message | optical      |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |


### Electrical properties

|                         |               |
|-------------------------|---------------|
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |
|-------------------------|---------------|

### Connection data

|                   |                          |
|-------------------|--------------------------|
| Connection method | VALVETRAB plug-in system |
|-------------------|--------------------------|

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 17.5 mm                                                                              |
| Height              | 52.4 mm                                                                              |
| Depth               | 55.3 mm                                                                              |
| Horizontal pitch    | 1 Div.                                                                               |

### Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0              |
| CTI value of material                  | 600              |
| Insulating material                    | PA 6.6/PBT       |
| Material group                         | I                |
| Housing material                       | PA 6.6           |
|                                        | PBT              |

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

## Protective circuit

|                                                    |                                     |
|----------------------------------------------------|-------------------------------------|
| Mode of protection                                 | L-N                                 |
|                                                    | L-PEN                               |
|                                                    | N-PE                                |
| Direction of action                                | 1L-N/PE                             |
| Nominal voltage $U_N$                              | 240/415 V AC (TN-C, TN-S)           |
| Nominal frequency $f_N$                            | 50 Hz (60 Hz)                       |
| Maximum continuous operating voltage $U_C$         | 385 V AC                            |
| Protective conductor current $I_{PE}$              | $\leq 450 \mu A$                    |
| Standby power consumption $P_C$                    | $\leq 175 \text{ mVA}$              |
| Nominal discharge current $I_n$ (8/20) $\mu s$     | 20 kA                               |
| Maximum discharge current $I_{max}$ (8/20) $\mu s$ | 40 kA                               |
| Short-circuit current rating $I_{SCCR}$            | 25 kA                               |
| Voltage protection level $U_p$                     | $\leq 1.8 \text{ kV}$               |
| Residual voltage $U_{res}$                         | $\leq 1.8 \text{ kV}$ (at $I_n$ )   |
|                                                    | $\leq 1.6 \text{ kV}$ (at 10 kA)    |
|                                                    | $\leq 1.4 \text{ kV}$ (at 5 kA)     |
|                                                    | $\leq 1.3 \text{ kV}$ (at 3 kA)     |
| TOV behavior at $U_T$                              | 415 V AC (5 s / withstand mode)     |
|                                                    | 440 V AC (120 min / withstand mode) |
| Max. backup fuse with branch wiring                | 100 A (gG)                          |

## Additional technical data

|                                                    |       |
|----------------------------------------------------|-------|
| Maximum discharge current $I_{max}$ (8/20) $\mu s$ | 40 kA |
|----------------------------------------------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                           |
|-----------------------------------------|-----------------------------------------------------------|
| Degree of protection                    | IP20                                                      |
| Ambient temperature (operation)         | -40 °C ... 80 °C                                          |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C                                          |
| Altitude                                | $\leq 2000 \text{ m}$ (amsl)                              |
| Permissible humidity (operation)        | 5 % ... 95 %                                              |
| Shock (operation)                       | 25g (Half-sine / 11 ms / 3x $\pm X$ , $\pm Y$ , $\pm Z$ ) |
| Vibration (operation)                   | 5g (10 ... 500 Hz / 2.5 h / X, Y, Z)                      |

## Approvals

### UL specifications

|                                           |          |
|-------------------------------------------|----------|
| Maximum continuous operating voltage MCOV | 385 V AC |
| Short-circuit current rating (SCCR)       | 200 kA   |
| Voltage protection rating VPR             | 1200 V   |
| UL type                                   | type 1   |
| Nominal discharge current $I_n$           | 20 kA    |
| Maximum Surge Current per Phase           | 40 kA    |

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

|                           |              |
|---------------------------|--------------|
| Mode of protection        | L-N          |
|                           | L-G          |
|                           | N-G          |
| Nominal voltage           | 277/480 V AC |
| Power distribution system | Single phase |
| Nominal frequency         | 50/60 Hz     |
| SPD Type                  | 1CA          |

## Standards and regulations

### Air clearances and creepage distances

|                          |                          |
|--------------------------|--------------------------|
| Standards/regulations    | EN 60664-1 / EN 61643-11 |
| Standards/specifications | IEC 61643-11             |
| Note                     | 2011                     |
| Standards/specifications | EN 61643-11              |
| Note                     | 2012                     |

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|


# VAL-US-277/40-P - Type 1 surge protection plug

2910338

<https://www.phoenixcontact.com/nl/products/2910338>



## Drawings



Circuit diagram



# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2910338>



**cUL Recognized**  
Approval ID: FILE E 330181



**UL Recognized**  
Approval ID: FILE E 330181

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171292 |
| ECLASS-15.0 | 27171292 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002496 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

# VAL-US-277/40-P - Type 1 surge protection plug



2910338

<https://www.phoenixcontact.com/nl/products/2910338>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.  
Hengelder 56 6902 PA Zevenaar  
Postbus 246 6900 AE Zevenaar  
(0316) 59 17 20  
[sales@phoenixcontact.nl](mailto:sales@phoenixcontact.nl)