



Extract from the online catalog

SAC-3P-M12MS/0,3-PUR/A-1L-S

Order No.: 1669071



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1669071>

Sensor/Actuator cable, 3-position, PUR/PVC, Black RAL 9005, Plug, straight M12, A-coded, on Valve plug A, with 1 LED, connected with Z diode, Cable length: 0.3 m

Commercial data	
EAN	4017918135966
Note	Made-to-order
sales group	D113
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.0595 KG
Catalog page information	Page 90 (PC-2007)

Product notes

WEEE/RoHS-compliant since:
12/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data	
Nominal current I_N	4 A
Nominal voltage U_N	24 V
Number of positions	3
Volume resistance	5 mΩ

SAC-3P-M12MS/0,3-PUR/A-1L-S Order No.: 1669071
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1669071>

Insulation resistance	≥ 100 MΩ
Length of cable	0.3 m
Ambient temperature (operation)	-25 °C ... 90 °C (plug/socket)

General characteristics

Coding	A - standard
Surge voltage category	II
Pollution degree	3
Degree of protection	IP67
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ag
Valve plug contact insert material	PBT
Material, housing, valve plug	PBT
Material, knurls	Zinc die-cast, (nickel-plated)
Sealing material	TPU (Flat gasket valve plug)
Status display	1 LED
Protective circuit/component	Z diode

Conductor data


Cable type	PUR/PVC black
Cable abbreviation	LIYY11Y-JZ
Conductor cross section	0.75 mm ²
AWG signal line	18
Conductor structure signal line	42x 0.15 mm
Core diameter including insulation	Approx. 1.8 mm
Thickness, insulation	Approx. 0.34 mm (Core insulation)
	Approx. 0.35 mm (Outer cable sheath)
	Approx. 0.3 mm (Inner sheath)
External cable diameter	5.90 mm
Wire colors	Black 1, black 2, green/yellow
External sheath, color	Black RAL 9005
Insulation resistance	≥ 1 MΩ*km

SAC-3P-M12MS/0,3-PUR/A-1L-S Order No.: 1669071
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1669071>


Nominal voltage, conductor	300 V
Test voltage, conductor	2000 V
Overall twist	3 concentrically twisted wires
Outer sheath, material	PUR
Material, inner sheath	PVC
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Smallest bending radius, movable installation	59 mm

Diagrams/Drawings

Dimensioned drawing




M12 x 1 male connector, straight




Valve plug, type A


Circuit diagram



Schematic diagram



Pin assignment M12 plug, 3-pos., valve connector



Valve connector pin assignment, type A

onlinecomponents.com

SAC-3P-M12MS/0,3-PUR/A-1L-S Order No.: 1669071
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1669071>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com