




Extract from the online catalog

MCV 1,5/ 9-G-3,5-RN

Order No.: 1731552

The figure shows a 10-position version of the product




<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1731552>

Header, Nominal current: 8 A, Rated voltage (III/2): 160 V, Pitch: 3.5 mm, Color: green, Assembly: Soldering

Commercial data	
GTIN (EAN)	4046356158992
Note	Made-to-order
sales group	E100
Pack	50 pcs.
Customs tariff	85366990
Weight/Piece	0.00247 KG

Product notes

WEEE/RoHS-compliant since: 09/21/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data


Dimensions / positions	
Length	7.25 mm
Pitch	3.5 mm
Dimension a	28 mm
Number of positions	9
Pin dimensions	0,8 x 0,8 mm

MCV 1,5/ 9-G-3,5-RN Order No.: 1731552
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1731552>

Hole diameter	1.2 mm
Technical data	
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/2)	160 V
Rated voltage (II/2)	250 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	8 A
Nominal voltage U_N	160 V
Maximum load current	8 A
Insulating material	PBT
Inflammability class acc. to UL 94	V0


Diagrams/Drawings

Drilling plan/solder pad geometry



MCV 1,5/ 9-G-3,5-RN Order No.: 1731552
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1731552>

Dimensioned drawing



onlinecomponents.com

MCV 1,5/ 9-G-3,5-RN Order No.: 1731552
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1731552>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com