
AKG 35 GN - Connection terminal block

3062993

https://www.phoenixcontact.com/nl/products/3062993

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection terminal block, nom. voltage: 300 V, nominal current: 125 A, connection method: Screw connection, Rated cross section: 35 mm^2, cross section: 2.5 mm^2 - 35 mm^2, mounting: Neutral busbar, color: green

Commercial data

Item number	3062993
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE7331
Product key	BE7331
GTIN	4046356558389
Weight per piece (including packing)	20,2 g
Weight per piece (excluding packing)	20,2 g
Customs tariff number	85369010
Country of origin	PL

Technical data

Product properties

Number of connections	1
Number of rows	1

Electrical properties

Maximum load current	125 A (with 35 mm² conductor cross-section)
Maximum power dissipation for nominal condition	4.06 W
Nominal current I_N	125 A
Current carrying capacity of the neutral busbar	140 A


Connection data

Nominal cross section	35 mm²
Maximum load current	125 A (with 35 mm² conductor cross-section)

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M6
Tightening torque	3.2 ... 3.7 Nm
Stripping length	16 mm
Connection in acc. with standard	IEC / EN
Conductor cross-section rigid	2.5 mm² ... 35 mm²
Cross section AWG	12 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	2.5 mm² ... 35 mm²
Conductor cross-section, flexible [AWG]	12 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	2.5 mm² ... 35 mm²
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm² ... 35 mm²
2 conductors with same cross section, rigid	1.5 mm² ... 16 mm²
2 conductors with same cross section, flexible	1.5 mm² ... 16 mm²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm² ... 16 mm²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm² ... 10 mm²
Nominal cross section	35 mm²
Nominal current	125 A
Maximum load current	125 A (with 35 mm² conductor cross-section)
Nominal voltage	300 V

Dimensions

Dimensional drawing	
Width	14.3 mm
Height	27 mm
Depth	39 mm
Length	27 mm

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V2
Insulating material	PA

Standards and regulations


Connection in acc. with standard	IEC / EN

Mounting


Mounting type	Neutral busbar

Drawings

Dimensional drawing



Dimensional drawing



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/nl/products/3062993

CSA
Approval ID: 13631

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	-	135 A	18 - 2	-

UL Recognized
Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	-	115 A	18 - 2	-
C				
	-	115 A	18 - 2	-
F				
	-	115 A	18 - 2	-

EAC
Approval ID: KZ7500651131219505

Classifications

ECLASS

ECLASS-13.0	27250116
ECLASS-15.0	27250116

ETIM

ETIM 10.0	EC000001

UNSPSC

UNSPSC 21.0	31162900

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl