




Extract from the online catalog

QC 0,5/ 7-STF-3,81

Order No.: 1897597

The figure shows a 10-position version of the product



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1897597>

Plug component, Nominal current: 6 A, Nom. voltage: 320 V, Pitch: 3.81 mm, Number of positions: 7, Connection type: Insulation displacement connection QUICKON, Color: green

Commercial data	
EAN	4017918165093
Pack	50 pcs.
Customs tariff	85366990
Weight/Piece	0.00731 KG
Catalog page information	Page 157 (CC-2009)

Product notes

WEEE/RoHS-compliant since: 01/01/2003



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions / positions	
Pitch	3.81 mm
Dimension a	22.86 mm
Number of positions	7

QC 0,5/ 7-STF-3,81 Order No.: 1897597
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1897597

Technical data

Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A
Nominal voltage U_N	320 V
Nominal cross section	0.5 mm ²
Maximum load current	6 A (with 0.5 mm ² conductor cross section)
Insulating material	PA
Inflammability class acc. to UL 94	V0

Connection data

Conductor cross section stranded min.	0.34 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section AWG/kcmil min.	22
Conductor cross section AWG/kcmil max	20

Certificates / Approvals



Certification CB, CUL, GOST, UL, VDE-PZI

CUL

Nominal voltage U_N	300 V
Nominal current I_N	6 A
AWG/kcmil	24-20


UL

Nominal voltage U_N	300 V
Nominal current I_N	6 A
AWG/kcmil	24-20

QC 0,5/ 7-STF-3,81 Order No.: 1897597
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1897597>

Drawings

Dimensioned drawing



onlinecomponents.com

QC 0,5/ 7-STF-3,81 Order No.: 1897597
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1897597>

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com