



Extract from the online catalog

ST-REL2-KG120/1AU

Order No.: 2823751

The illustration shows version ST-REL 2-KG 24/1 AU



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2823751>

Relay connector, equipped with miniature switching relay, contacts (AgPd60): small loads, 1 N/O contact, input voltage 120 V AC/DC, with light indicator, can be plugged on basic termination blocks

Commercial data	
EAN	4017918077570
Pack	10 pcs.
Customs tariff	85364900
Weight/Piece	0.03498 KG
Catalog page information	Page 87 (IF-2005)

Product notes

WEEE/RoHS-compliant since:
08/10/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

ST-REL2-KG120/1AU Order No.: 2823751
http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2823751

Technical data

Coil side

Nominal input voltage U_N	120 V AC/DC
Input voltage range in reference to U_N	0.8 ... 1.06
Nominal input current at U_{IN}	5 mA
Typical response time	7 ms (with DC)
Typical release time	11 ms (with DC)
Operating voltage display	Yes
Protective circuit/component	Bridge rectifier, varistor

Contact side

Contact type	Double contact, 1 N/O contact
Contact material	Silver palladium (AgPd60), 5 µm hard gold-plated
Maximum switching voltage	30 V AC 36 V DC
Maximum inrush current	0.2 A
Limiting continuous current	0.5 A
Interrupting rating (ohmic load) max.	5 W (for 24 V DC)
Note	the following values are applicable if a gold layer is destroyed
Maximum switching voltage	125 V AC
Limiting continuous current	2 A
Maximum inrush current	2 A
Interrupting rating (ohmic load) max.	29 W (for 24 V DC) 29 W (for 48 V DC) 29 W (for 60 V DC) 60 VA (for 250 V AC)

General data

Width	14.6 mm
Height	66.5 mm
Depth	33 mm
Test voltage relay winding/relay contact	2.5 kV AC (50 Hz, 1 min.)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Operating mode	100% operating factor

ST-REL2-KG120/1AU Order No.: 2823751

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2823751>

Service life mechanical	Approx. 2×10^7 cycles
Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
	IEC 60255/DIN VDE 0435 (in relevant parts)
	DIN EN 50178/DIN VDE 0160 (in relevant parts)
	EN 60730/DIN VDE 0631
	DIN VDE 0160 (in relevant parts)

Certificates / Approvals



Certification


GOST

onlinecomponents.com

ST-REL2-KG120/1AU Order No.: 2823751
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2823751>

Drawings

Circuit diagram



ST-REL2-KG120/1AU Order No.: 2823751
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2823751>

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com