



Extract from the online catalog

UPBV 4/ 5

Order No.: 3045842

The illustration shows the 6-position version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3045842>

COMBI plugs, Type of connection: Screw connection, Screw connection, Number of positions: 5, Cross section: 0.14 mm² - 6 mm², AWG 26 - 10, Width: 31 mm, Height: 47 mm, Color: gray

Commercial data	
EAN	4046356083355
Pack	50 pcs.
Customs tariff	85369010
Weight/Piece	0.03104 KG
Catalog page information	Page 277 (CL-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions	
Width	31 mm
Length	21 mm
Height	47 mm

UPBV 4/ 5 Order No.: 3045842

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3045842>

Technical data

Maximum load current	32 A (with 6 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61 984
Nominal current I _N	32 A
Nominal voltage U _N	800 V
Number of positions	5

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²

UPBV 4/ 5 Order No.: 3045842

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3045842>

Type of connection	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

Certificates / Approvals



Certification

CUL, UL

CUL


Nominal voltage U_N	600 V
Nominal current I_N	30 A
AWG/kcmil	26-10

UL

Nominal voltage U_N	600 V
Nominal current I_N	30 A
AWG/kcmil	26-10

Drawings

Diagram



The figure shows the derating curve of the UT 4/1P... terminal block in connection with the UPVB 4 connector

UPBV 4/ 5 Order No.: 3045842

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3045842>

Circuit diagram



onlinecomponents.com

UPBV 4/ 5 Order No.: 3045842

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3045842>

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com