



NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 600V MAX. VOLTAGE RATING.
 - B. AMPERAGE LISTED IN TABLE.
2. SLOTTED HEAD SCREW USED IF HEX SIZE IS NOT GIVEN.
3. PACKAGE QTY. -Q=25
-C=100
4. ADDITIONAL MULTIPLE WIRE COMBINATIONS FOR CX70-14-C ARE:
 - A. TWO-#14'S
 - B. TWO-#12'S
5. PANDUIT PART NUMBERS WITH A "T" ARE TIN PLATED.



PANDUIT PART NUMBR	DIMENSIONS ± .02									MAX. AMERAGE RATING	MARKINGS		HEX SIZE	C (MAX)
	G	W	K	A	M	T	H	L	E		LINE 1	LINE 2		
CX35-36-C	.22	.38	.19	1.02	.38	.07	.48	.35	.20	35	CX-35	6-14	SCREW	.22
CX35-36T-C	.22	.38	.19	1.02	.38	.07	.48	.35	.20	35	CX-35	6-14	SCREW	.22
CX70-14-C	.31	.50	.25	1.27	.50	.08	.57	.46	.27	70	CX-70	4-14	SCREW	.28
CX70-14T-C	.31	.50	.25	1.27	.50	.08	.57	.46	.27	70	CX-70	4-14	SCREW	.28
CX125-14-Q	.43	.62	.31	1.53	.62	.13	.77	.57	.27	125	CX-125	1/0-4	SCREW	.41
CX125-56T-Q	.43	.62	.31	1.53	.62	.13	.77	.57	.34	125	CX-125	1/0-4	SCREW	.41
CX225-56-Q	.56	1.00	.50	2.19	1.00	.13	1.13	.85	.34	225	CX-225	4/0-2	9/16	.50
CX225-56T-Q	.56	1.00	.50	2.19	1.00	.13	1.13	.85	.34	225	CX-225	4/0-2	9/16	.50
CX225-38T-Q	.56	1.00	.50	2.19	1.00	.13	1.13	.85	.38	225	CX-225	4/0-2	9/16	.50
CX400-38-3	.88	1.50	.75	3.16	1.38	.19	1.65	1.13	.44	400	CX-400	500kcmil-4/0	3/4	.81
CX400-12T-3	.88	1.50	.75	3.16	1.38	.19	1.65	1.13	.50	400	CX-400	500kcmil-4/0	3/4	.81

C41303_06

06	4/04	TLCO													
05	03/03	SRB	JAC	Updated "L" dimensions to match current product offering				10739	JAC	LSM					
REV	DATE	BY	CHK	DESCRIPTION				ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.	



TINLEY PARK, ILLINOIS

"CX" SERIES COPPER MECHANICAL LUGS

DRAWN BY EJS CHK'D SKB SCALE NONE DRAWING NO. C41303