



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	B HEIGHT	IMPRINT AREA C	VERTICAL REPEAT D	LABELS PER ROW	STANDARD PKG. QTY.
S100X075TAT	GMT1	0.750 [19.0]	0.25 +/- .031 [6.35]	1.000 [25.4]	4	2500
S100X125TAT	GMT1	1.250 [31.8]	0.38 +/- .031 [9.53]	1.500 [38.1]	4	2500
S100X150TAT	GMT1	1.500 [38.1]	0.50 +/- .031 [12.7]	1.800 [45.7]	4	2500
S100X225TAT	GMT1	2.250 [57.2]	0.75 +/- .031 [19.0]	2.500 [63.5]	4	1500



UNWIND
DIRECTION

NOTES:
1. SEE MFG. DRAWING NO. A61298.
2. MILLIMETERS ARE IN [].

CAD FILENAME/LAYERS: I00472GU_A61298_S100XxxxTAT_00.prt

PANDUIT CORP TINLEY PARK, ILLINOIS

OPTIMUM SELF-LAM. S100X***TAT
THERMAL TRANSFER PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .031 (,.XXX) ± .005
(.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

DRAWN BY: RVU

MAT'L:

SCALE

NTS

DATE: 10-12-04

SEE TABLE

DRAWING NO.

C10347

ORG

B

SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	10-12-04	RVU		DRAWING RELEASED.	0000	R		