


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HEADER
SIDE
SPLIT
DOOR



.9
[23]

PANDUIT P/N	WEIGHT
CNDS	38 LBS/EACH 17.2 Kg/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- PARTS SUPPLIED:
1 - HANDLE SIDE SECTION
1 - HEADER SIDE SECTION
- DIMENSIONS IN PARENTHESIS ARE METRIC.

PERFORATION
AREA OF DOOR

PERFORATION
AREA OF DOOR

81.2
[2063]

FRONT

LOCKABLE
SWING HANDLE

SIDE

MODEL FILENAME V10395AX_32_SP-DR_FG_ASSY_00.PRT

CAD FILENAME/LAYERS V10395AX_DC_00A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

SPLIT DOORS
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015
 [METRIC - MILLIMETER] X.X +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4
 ANGLE +/- 1°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LEE

MAT'L:

SCALE NONE

DATE
1-10-07

SEE
NOTES

DRAWING NO.

10395-29

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
00	1-10-07	LEE		RELEASED TO PRODUCTION	10395-29				