

Search Results

Evaluate

- FAQ's
- Selection Guides
- PDFConvenience..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DNF14-250M-E'

Your search criteria matched only one product, shown below

DNF14-250M-E



- Male tab couples with (all 0.250 x 0.032) female disconnects
- Male tab can be inserted and removed from the female disconnect without the use of tools for lower installed cost
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
- Rated up to 600 V

Part Number	DNF14250M-E
RoHS Compliancy Status	Compliant
Part Description	Male Disconnect, nylon barrel insulated, funnel entry, 16- 14 AWG, .250 x .032 tab.
Product Type	Disconnects
CSA Certified	Yes
Length (In.)	0.90
Length (mm)	22.9
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.162
Max. Ins. (mm)	4.12
Panduit Color Code	Blue
Plating Type	Nickel
Pricing Description	Terminal Convenience Package
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.3 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-1550, CT-1551, CT-2500
Wire Range	16 – 14 AWG
Wire Range (mm ²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.