

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'LAMA800-58-6Y'

Your search criteria matched only one product, shown below

**LAMA80058-6Y**



For Use with Stranded Aluminum or Copper Code Conductors

- Made from high strength, extruded aluminum alloy to provide premium electrical and mechanical performance
- Tin-plated to inhibit corrosion
- Compact design saves space
- Wide wire range -taking capability minimizes inventory requirements
- Inspection window to visually assure full conductor insertion
- Plated steel or aluminum set screw provides high strength, durable electrical contact between conductor and connector
- UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90°C

Note: These code conductor mechanical lugs are manufactured for use with AWG wire only.

Part Number	LAMA800-58-6Y
RoHS Compliancy Status	Compliant
Note	LAMA800-58-6Y replaces LAMA800-58-6
Part Description	Aluminum, single barrel, onehole tongue connector, type LAMA.
Product Type	Mechanical Connectors- Lugs
Material	Tin-Plated Aluminum
CSA Certified	No
UL Listed	Yes
Height (In.)	1.94
Height (mm)	49.3
Length (In.)	3.38
Length (mm)	85.9
Stud Hole Size (In.)	5/8
Tongue Width (In.)	1.63
Aluminum or Copper Conductor Size Range	350 kcmil– 800 kcmil
CE Compliant	No
Conductor Size Range (mm <sup>2</sup> )	185 – 500
Hex Key Size (In.)	9/16
Pricing Description	Aluminum Mechanical Lug, 1 Hole, 1 Barrel, 350 800 kcmil, 5/8" (15.9mm) Stud
Tightening Torque (InLbs)	See product packaging
Tightening Torque (Nm)	See product packaging
Tongue Length	1.75
Tongue Length (mm)	44.5
Tongue Thickness	0.38
Tongue Type	Straight
Tongue Width (mm)	41.4
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.