

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF Copper, Long..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

Part Description > Flex lug, long barrel, #6 AWG, 2hole, 1/4" stud holes, .75 hole spacing, 45° angle tongue.

Your search criteria matched only one product, shown below


LCCX6-14BH-L



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

| | |
|------------------------------|--|
| Part Number | LCCX6-14BH-L |
| RoHS Compliancy Status | Compliant |
| Part Description | Flex lug, long barrel, #6 AWG, 2hole, 1/4" stud holes, .75 hole spacing, 45° angle tongue. |
| Material | Tin-Plated Copper |
| CSA Certified | Yes |
| UL Listed | Yes |
| Length (In.) | 2.31 |
| Length (mm) | 58.7 |
| Class G,H, I, K, M | #6 AWG |
| Diesel Locomotive | #6 AWG |
| Stud Hole Size (In.) | 1/4 |
| Stud Hole Spacing (In.) | 0.75 |
| Tongue Width (In.) | 0.48 |
| Barrel Length (In.) | 1.07 |
| Angle | 45° |
| Barrel Length (mm) | 27.2 |
| CE Compliant | No |
| Panduit Color Code | Blue |
| Panduit Die Index No. | P24 |
| Pricing Description | Copper Compression Lug, 2 Hole, #6 AWG Flex, 1/4" (6.4mm) Stud, 45° Bent |
| Stud Hole Size (mm) | 6.4 |
| Tongue Thickness | 0.08 |
| Tongue Type | Standard |
| Tongue Width (mm) | 12.2 |
| Wire Strip Length (In.) | 1 1/8 |
| Wire Strip Length (mm) | 29.0 |
| Min. Order UOM | PC |
| Min. Order Qty. | 1 |
| Burndy Die Index No. | 7 |
| T&B Die Index No. | 24 |
| BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| Add to Favorite Product List |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.