

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDF Copper Butt ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results

 **Text Search: 'SCS250-X'**


Your search criteria matched only one product, shown below

SCS250-X



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

Part Number	SCS250-X
RoHS Compliancy Status	Compliant
Part Description	Copper Butt Splice, standard barrel, 250 kcmil cable.
Product Type	Compression Connectors- Splices
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.25
Length (mm)	57.2
Copper Conductor Size	250 kcmil
Barrel O.D.	.77
Barrel I.D.	.63
Panduit Color Code	Yellow
Panduit Die Index No.	P62
Pricing Description	Copper Compression Butt Splice, Standard Barrel, 250 kcmil
Wire Strip Length (In.)	1 1/16
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	16
T&B Die Index No.	62
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.