

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFNon-Shrink P ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'TV105-3MY'

Your search criteria matched only one product, shown below

TV105-3MY




Non-Shrink oil resistant flexible clear tubing on reel

- Provides insulation and protection for lead wires wire harness assemblies soldered joints and components in electrical and electronic equipment
- Material: Polyvinyl chloride (PVC)
- Voltage Rating: 300V and 600V
- All purpose flexible non -shrinkable
- Resistant to heat and moisture

Applicable Specifications:

- UL224 VW-1
- CSA C22.2 No. 198.1 (OFT)
- ASTM D-922 Grade CFR
- MIL-I-631 Type F, Form U, Grade C- Class 1 Category 1

▪ Part Number	TV105-3MY
▪ RoHS Compliance Status	Compliant
▪ Note	TV105-3MY replaces TV105-4TLY
▪ Part Description	PVC Non-Shrink Tubing, 105°C rated
▪ Material	Polyvinyl Chloride
▪ Color	Clear
▪ CSA Certified	Yes
▪ CSA Specification	CSA C22.2 No. 198.1 (OFT)
▪ UL Recognized	E122770
▪ UL Recognized Specification	UL224 VW-1
▪ Flammability Rating	UL224 VW-1
▪ Length Per Reel (ft.)	1000
▪ Length Per Reel (m)	304.8
▪ Max. Inside Diameter (In.)	.249
▪ Max. Inside Diameter (mm)	6.32
▪ Max. Voltage Rating	300 V
▪ Min. Inside Diameter (mm)	5.82
▪ Minimum Inside Diameter (In.)	.229
▪ Nominal Size	3 AWG
▪ Pricing Description	Vinyl Tubing, 3 AWG (6.32mm) 300V, Clear
▪ Temperature Range	-4°F to 221°F (-20°C to 105°C)
▪ Wall Thickness (In.)	.020
▪ Wall Thickness (mm)	.51
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.