



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Drawings
 - PDFNon-Shrink P ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips € Within Results

Text Search: 'TV105-6M20Y'

Your search criteria matched only one product, shown below

TV105-6M20Y



- Non-Shrink oil resistant flexible clear tubing on reel
- Provides insulation and protection for lead wires wire harness assemblies soldered joints and components in electrical and electronic equipment
 - Material: Polyvinyl chloride (PVC)
 - Voltage Rating: 300V and 600V
 - All purpose flexible non -shrinkable
 - Resistant to heat and moisture
- Applicable Specifications:
- UL224 VW-1
 - CSA C22.2 No. 198.1 (OFT)
 - ASTM D-922 Grade CFR
 - MIL-I-631 Type F, Form U, Grade C- Class 1 Category 1

Part Number	TV105-6M20Y
RoHS Compliance Status	Compliant
Note	TV105-6M20Y replaces TV105-7D20Y
Part Description	PVC NonShrink Tubing, 105°C rated
Material	Polyvinyl Chloride
Color	Black
CSA Certified	Yes
CSA Specification	CSA C22.2 No. 198.1 (OFT)
UL Recognized	E122770
UL Recognized Specification	UL224 VW-1
Flammability Rating	UL224 VW-1
Length Per Reel (ft.)	1000
Length Per Reel (m)	304.8
Max. Inside Diameter (In.)	.178
Max. Inside Diameter (mm)	4.52
Max. Voltage Rating	300 V
Min. Inside Diameter (mm)	4.11
Minimum Inside Diameter (In.)	.162
Nominal Size	6 AWG
Pricing Description	Vinyl Tubing, 6 AWG (4.52mm), 300V Black
Temperature Range	-4°F to 221°F (20°C to 105°C)
Wall Thickness (In.)	.020
Wall Thickness (mm)	.51
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	€

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.