Search Results

Evaluate
- FAQ's
- Press Releases
- Stainless St..
- Product Bulletins
- PDF Stainless St..

Design a Solution
- Part Drawings
- PDF MLT, Heavy S..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'MLTFC6H-LP316RD'**

Your search criteria matched only one product, shown below

MLTFC6H-LP316RD

- Polyester coating available in six color options provides visual indication for easy identification in color-coding applications (heavy cross section only)
- Self-locking head design speeds installation and locks into place at any length along the tie body
- Polyester coating provides additional edge protection and prevents corrosion between dissimilar metals
- AISI 316 stainless steel for the most corrosive environments
- Available in standard, heavy, extra-heavy and super-heavy cross sections
- UV resistant, low smoke, halogen -free material
- Temperature tolerance -40°F (-40°C) to 302°F (150°C)

Part thickness is base material less coating.

Part Number	MLTFC6H-LP316RD
RoHS Compliancy Status	Compliant
Part Description	Polyester coated stainless steel tie, AISI 316, heavy, 20.5" length.
Product Type	Stainless Steel Cable Tie
Material	Stainless Steel Type 316 (V4A)
Color	Red
Length (In.)	20.5
Length (mm)	521
Width (In.)	0.31
Width (mm)	7.9
Max. Bundle Diameter (In.)	6.0
Max. Bundle Diameter (mm)	152
Min. Bundle Diameter (In.)	0.50
Min. Bundle Diameter (mm)	12.7
Min. Loop Tensile Strength (Lbs.)	250
Min. Loop Tensile Strength (N)	1112
Pricing Description	MLT Tie, 316 SS, Fully Coated, Heavy, 20.5" (521mm), .010" (.25mm) thk, Red
Temperature Range	-40°C – 150°C
Thickness (In.)	0.010
Thickness (mm)	0.25
Tool	GS4MT, ST2MT, HTMT, PPTMT, PBTMT
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2010, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy