


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFQL0D2Q0BA241..
 - Part Drawings
 - PDFSwitched POU..
 - Specification Sheets
 - PDF16 and 32 Am..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
 - Installation Instructions
 - PDFPanduit POU.
 - Operation Manuals
 - PDFPViQ Switches..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'QL0D2B2BN24R1'

Your search criteria matched only one product, shown below


QL0D2B2BN24R1



- Remote switching capability for power cycling individual outlets or a group of outlets on or off to reboot equipment or power off individual outlets to stop unauthorized use
- Per outlet monitoring provides data to determine if power allocations are accurate and the efficiency metric of any server in the data center allowing individual servers to be identified as candidates for additional capacity, redeployment, or decommissioning
- Time delay sequencing avoids circuit overload due to high in-rush current at equipment start up
- Remote access to power consumption data via a web-based GUI provides global network access to real-time power information
- Integrates with Panduit® PIM™ Software which aggregates power information through a single web based GUI
- Measure in-cabinet temperature, humidity, airflow, and dew point remotely to prevent environmental factors that can cause equipment to overheat or malfunction
- Alarm messaging capability provides user-defined alarm/messaging capabilities for specific

events that exceeded thresholds

- Each outlet has a green LED for indication if the outlet is on or off for easy visual identification
- Optional remote LED display available for local monitoring, part number PVQ -RD
- Outlet Group Overload Protection allows user defined amperage threshold for a group of outlets to prevent accidental circuit breaker overload

Part Number	QL0D2B2BN24R1
RoHS Compliancy Status	Compliant
Part Description	Vertical power strip 32 A, 230V, 24 IEC C-13 and 6 IEC G19 receptacles, RJ-45 Ethernet port with two RJ12 remote environmental ports, two 16 A double pole magnetic breaker on/off switch with integral switch guard, and 3m power cord with IEC 60309 - 2P+E pin in sleeve connector. Complies with IEC 609501, EN 55022, EN 55024 and CE Marked. Dimensions: 66.3"H x 2.0"W x 2.25"D (1683mm x 51mm x 58mm)
Product Type	Vertical Power Outlet Unit
Color	Black
CE Compliant	Yes
Plug Type	IEC 60309- 2P + E
Pricing Description	Vertical, Mixed (18) C-13 & (6) C-19, Switched with Per Outlet Power & Environmental Monitored 230V, 32A SinglePhase POU
Min. Order UOM	PC
Min. Order Qty.	1
Voltage	230V
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.