



enabling technologies

[10 Gig Ethernet](#)
[Data Centers](#)
[Fiber System Deployment](#)
[Grounding System for Data Centers](#)
[Industrial Ethernet](#)
[Managing the Physical Layer](#)
[Network Security](#)
[Power Over Ethernet](#)

product information

[Products](#)
[Bill of Material](#)
[My Catalog](#)
[Part Search](#)
[Cross Reference](#)
[FAQ's](#)
[Download / Request Literature](#)
[Downloads](#)

resources to help you

[Evaluate Technologies](#)
[Design a Solution](#)
[How to Buy](#)
[Evaluate, Design & Install Products](#)
[Download Panduit Logo](#)
[White Papers](#)
[RoHS Compliance](#)

value added services

[Strategic Alliance Program](#)
[Consultants](#)
[Distributors](#)
[Installers](#)
[System Integrators](#)
[Warranties](#)

Product Information: Products

[USA](#) | [Identification and Labeling Products](#) | [Thermal Transfer Labels](#) | [Component Thermal Transfer Labels](#) |

Thermal Transfer Component Labels



- Sizes for electrical and electronic applications
- Available in several industrial materials
- Labels are provided on 3.0" (76.2 mm) cores and must be rear fed from PTR2-RS External Roll Stand

Part Number	TTC5Y-10
Product Family	Thermal Transfer Component Labels
RoHS Compliant	Compliant
Part Description	Thermal Transfer Label, 0.75" x 0.25", Polyester, White
Material	Polyester
Color	White
Height (In.)	0.25
Height (mm)	6.4
Width (In.)	0.75
Width (mm)	19.1
Horizontal Repeat (In.)	0.80
Horizontal Repeat (mm)	20.3
Labels Per Row	4
Printer	Thermal Transfer
Roll Width (In.)	3.35
Roll Width (mm)	85.1
Std. Pkg. UOM	PK
Vertical Repeat (In.)	0.35
Vertical Repeat (mm.)	8.9
Web Width (In.)	3.35
Web Width (mm)	85.1
UOM	PC
Std. Pkg. Qty.	10000
Min. Order Qty	10000
BOM Qty. (# of Pkgs.)	

evaluate

[FAQs](#)

design a solution

install & maintain

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2005, PANDUIT CORP. All rights reserved.