



TABLE 1

DASH NO.	SHELL SIZE SERIES I	SHELL SIZE SERIES II	A THREAD	ØB MAX	C MAX	ØT MIN
08	09	08	7/16-28 UNEF	18,3	14,5	6,6
10	11	10	9/16-24 UNEF	21,5	18,0	10,1
12	13	12	11/16-24 UNEF	24,5	21,0	12,9
14	15	14	13/16-20 UNEF	27,8	24,2	16,1
16	17	16	15/16-20 UNEF	30,8	27,5	19,3
18	19	18	1 1/16-18 UNEF	34,1	30,7	21,7
20	21	20	1 3/16-18 UNEF	37,3	33,8	24,9
22	23	22	1 5/16-18 UNEF	40,5	36,9	28,1
24	25	24	1 7/16-18 UNEF	43,7	40,1	31,3

TABLE 2

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
1-G	ALUMINIUM / BLACK ANODISE, SULPHURIC
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

LIST NOT EXHAUSTIVE, SEE MATERIAL AND PLATING TABLE FOR FULL LIST

98F1-16-1-C

SERIES _____
 CONNECTOR INTERFACE _____
 ANGLE _____
 DASH NO. (TABLE 1) _____
 MATERIAL (TABLE 2) _____
 FINISH (TABLE 2) _____

DRAWN P.FRYER	DATE 17/11/2010	3RD ANGLE PROJECTION NOT TO SCALE	POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR				ASSY USED ON: MIL-DTL-38999 SERIES I & II TITLE: LOW PROFILE SPIN COUPLING ADAPTOR FOR OPEN WIRE BUNDLES	MATERIAL SEE TABLE 2
DESIGN APPR		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	PART NUMBER: 98F SERIES	NCAGE CODE U5792	DRAWING NO: P10260
QUAL APPR					
ISSUE 3	DCR 3969			WEIGHT —	GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°