




Extract from the online catalog

USLKG10 N-1

Order No.: 0442082



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0442082>

Ground modular terminal block, Type of connection: Screw connection, Screw connection, Cross section: 0.5 mm² - 16 mm², AWG 20 - 6, Width: 10.2 mm, Color: green-yellow, Mounting type: NS 35/15-2,3



Commercial data	
EAN	4017918117238
Pack	50 pcs.
Customs tariff	85369010
Weight/Piece	0.0324 KG
Catalog page information	Page 348 (CL-2009)

Product notes

WEEE/RoHS-compliant since: 06/23/2005

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Number of levels	1
Number of connections	2
Color	green-yellow

USLKG10 N-1 Order No.: 0442082

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0442082>

Insulating material	PA
Inflammability class acc. to UL 94	V0

Dimensions

Width	10.2 mm
Length	42.5 mm
Height NS 35/7,5	47 mm
Height NS 35/15	54.5 mm
Height NS 32	52 mm

Technical data

Maximum load current	76 A (with 16 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-2
Nominal current I _N	57 A
Open side panel	nein

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	10 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²

USLKG10 N-1 Order No.: 0442082

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0442082>

2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
Type of connection	Screw connection
Stripping length	10 mm
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

Certificates / Approvals



Certification CSA, CUL, GOST, UL

Certification Ex: IECEx, KEMA-EX

CSA

AWG/kcmil	24-6
-----------	------

CUL

AWG/kcmil	24-6
-----------	------

UL

AWG/kcmil	24-6
-----------	------

USLKG10 N-1 Order No.: 0442082
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0442082>

Diagrams/Drawings

Circuit diagram



Approbationslogos (EX-Bereich)



USLKG10 N-1 Order No.: 0442082

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0442082>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com