

LEC240 Series

240 W AC-DC DIN Rail Switching Power Supply



LEC240 Series is Bel Power Solutions AC-DC converter series featuring a cost-effective, energy efficient green power supply solution for standard DIN-rail mounting. The products offer a high level of stability and immunity to noise for industrial control equipment, machinery, and other industrial equipment in a variety of harsh environments.

These light weight AC-DC converters have an extremely compact design and the standard rail installation for space saving. Having good EMC performance, the series is compliant with international IEC/UL/BS EN 62368-1, UL 61010-1 standards for safety.

FEATURES

- Input voltage 85 - 264 VAC (universal)
- Output voltage 12 V, 24 V, 48 V (adjustable)
- Operating ambient temperature range -40°C to +70°C
- Efficiency up to 94%
- High reliability
- DC OK function
- Active PFC
- 150% peak load output for 3 seconds
- LED indicator for power on
- Output short circuit, over-current, over-voltage & over-temperature protection
- Operating altitude up to 5000 m
- OVC II
- UL 61010-1 safety certified
- Dimensions 41 x 124 x 110 mm (1.61 x 4.88 x 4.33 in)



APPLICATIONS

- Industrial control equipment
- Machinery
- Harsh environment applications



1. MODEL SELECTION

MODEL	INPUT VOLTAGE RANGE	OUTPUT VOLTAGE	MAX OUTPUT CURRENT	EFFICIENCY ¹	MAX. CAPACITIVE LOAD	MAX OUTPUT POWER ²
LEC240-12	85 - 264 VAC	12 V	16 A	92 %	160 000 µF	192 W
LEC240-24	85 - 264 VAC	24 V	10 A	94 %	40 000 µF	240 W
LEC240-48	85 - 264 VAC	48 V	5 A	94 %	10 000 µF	240 W

¹ Typical, at 230 VAC input

² See DERATING CURVES on page 4

2. INPUT SPECIFICATIONS

All specifications are measured at Ta = 25°C, humidity <75 % nominal input voltage and rated output load unless otherwise specified.

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Input voltage	AC Input	85		264	VAC
Input frequency		47		63	Hz
Input current	115 VAC 230 VAC			3 1.5	A
Inrush current ³	115 VAC 230 VAC		15 30		A
Power factor	115 VAC 230 VAC		0.98 0.94		
Leakage current	240 VAC			0.5	mA

³ Cold start

3. OUTPUT SPECIFICATIONS

All specifications are measured at Ta = 25°C, humidity <75 % nominal input voltage and rated output load unless otherwise specified.

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Adjustable output voltage ³	LEC240-12 LEC240-24 LEC240-48	12 24 48		14 28 53	VDC
Output current	LEC240-12 LEC240-24 LEC240-48			16 10 5	A
Output voltage accuracy ⁴	LEC240-12 LEC240-24 / LEC240-48		± 2 ± 1		%
Line regulation	Rated load		± 0.5		%
Load regulation	0% - 100% load		± 1		%
Ripple & noise ⁵	LEC240-12 LEC240-24 LEC240-48		50 60 75	100 120 150	mVpp
Stand-by power consumption			4		W
Hold-up time			20		ms
Switching frequency			100		kHz
DC-OK signal ⁶	30 VDC / 1 A max.				

³ The output voltage can be adjusted by the output adjustable resistance ADJ, turn clockwise.

⁴ At full load range

⁵ Measured with 20 MHz bandwidth, output parallel 47 µF electrolytic capacitor and 0.1 µF ceramic capacitor.

⁶ When the output voltage is normal, the relay is connected. As soon as the output voltage dips below 90% Vo, the relay is disconnected.



4. PROTECTIONS

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Short circuit protection	Constant current up to 1s, after 1s Hiccup mode applied. Auto recovery. Recovery time < 10s after the SC disappear.				
Over current protection ⁷	Normal / high temperature: auto recovery Low temperature: auto recovery	110 105		200	% I _o
Over voltage protection	V _{out} latch off (restart required)			18 35 60	V
Over temperature protection ⁸	OTP start OTP release (auto recovery)	60	80	90	°C

⁷ Constant current up to 1s, after 1s Hiccup mode applied.

⁸ 230 VAC, rated load

5. ENVIRONMENTAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Operating temperature		-40		+70	°C
Storage temperature		-40		+85	°C
Temperature derating	-40°C to -25°C +45°C to +70°C (115 VAC) +50°C to +70°C (230 VAC) +60°C to +70°C (230 VAC)	3.34 2.0 1.25 2.5			%/°C
Input voltage derating	AC Input voltage between 85 - 100 VAC / 120 - 140 VDC	0.67			%/VAC
Humidity	Operating, non-condescending Storage, non-condescending			90 95	%RH
Altitude	Operating Derating of 5°C / 1000 m for operating altitude > 2000 m			2000	m
MTBF	MIL-HDBK-217F @ 25 °C	300 000			hrs

6. EMC SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	CLASS / LEVEL / CRITERION
Conducted emissions	EN 55032 / CISPR 32	Class B
Radiated emissions	EN 55032 / CISPR 32	Class B
Harmonic current	IEC/EN 61000-3-2	Class A & Class D
ESD immunity	IEC/EN 61000-4-2, Contact ±8 kV / Air ±15 kV	Performance Criterion A
Radiated field immunity	IEC/EN 61000-4-3, 10 V/m	Performance Criterion A
Electrical fast transient	IEC/EN 61000-4-4, ± 4 kV	Performance Criterion A
Surge immunity	IEC/EN 61000-4-5, Line to line ±2 kV / Line to ground ±4 kV	Performance Criterion A
Conducted immunity	IEC/EN 61000-4-6, 10 V _{RMS}	Performance Criterion A
Voltage dips, interruptions	IEC/EN 61000-4-11, 0%, 70%	Performance Criterion B

7. SAFETY SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Safety standards & approvals	UL 61010-1, UL 61010-2-201 safety certified Design refers to IEC/UL/BS EN 62368-1				
Safety class	Class I				
Isolation test ⁹	Input to Ground Input to Output Output to Ground	2000 3000 500			VAC
Insulation resistance	At 500 VDC	50			MΩ

⁹ Electric strength test for 1 min., leakage current < 15 mA



Asia-Pacific
+86 755 298 85888

EMEA
+353 61 49 8941

North America
+1 866 513 2839

belfuse.com/power-solutions

8. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	MIN	TYP	MAX	UNIT
Dimensions			41 x 124 x 110 1.61 x 4.88 x 4.33		mm in
Weight			650		g
Case ¹⁰	Material: Metal (AL1100, SPCC) and Plastic (PC940)				
Cooling	Convection (Natural air flow)				

¹⁰ When the power supply is in use, the enclosure of the product needs to be connected to the system grounding.

9. DERATING CURVES




Figure 1. Temperature Derating Curve




Figure 2. Input Voltage Derating Curve




Figure 3. Efficiency vs Input Voltage Derating Curve (Full Load)





Figure 4. Efficiency vs Output Load Derating Curve (Vi = 230 VAC)

10. MECHANICAL DRAWINGS



All dimensions are in mm [in]
General tolerance ± 1.00 mm [± 0.039 in]
Wire range 26-10 AWG
Tightening torque max. 0.4 Nm
Mounting DIN Rail TS35
(rail needs to be connected to safety ground)

	PIN	FUNCTION
OUTPUT TERMINAL	1	-Vo
	2	-Vo
	3	+Vo
	4	+Vo
INPUT TERMINAL	5	AC (N)
	6	AC (L)
	7	
GROUNDING SCREW *		
DC ON LED		Output status indicator (green)
ADJ		Output adjustable resistor
DC OK SIGNAL		Monitors the output voltage on the output terminals

* Pin 7 and the grounding screw are interconnected.
Either Pin 7 or the grounding screw need to be
connected to earth.

Figure 5. Mechanical Drawing

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

